

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301090029](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Pro-Yellow® Nylon 26W Fluorescent Hand Lamp with Switch and Grips Molded, Cord Type 18/3 SJTW, Cord Length 15.24m (50.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E59049

General

Product Family Portable Lighting
 Series [130109](#)
 NEMA Configuration NEMA 5-15
 Outlet None
 Overview [Hand Lamps](#)
 Product Literature Order No 987650-8053
 Product Name Pro-Yellow®
 Type Hand Lamps
 UPC 78678852922
 Woodhead Yes

Physical

Cord Length - Primary 15.24m (50.0')
 Cord Length - Secondary N/A
 Depth N/A
 Duty Commercial
 Guard Included No
 Guard Type N/A
 Height N/A
 Length N/A
 Material - Guard Polycarbonate
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Fluorescent
 Cord Type - Primary 18/3 SJTW
 Lamp Type PL-C 26/41/4P
 Lamp Wattage - Maximum 26W
 Lumens 1800
 On/Off Switch Yes
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number WT6F-50



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130109 Series](#)