

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301090019](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Pro-Yellow® Nylon 13W Fluorescent Hand Lamp Only with Grips Molded 16/3 SJTW 6.10m (20.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E59049

General

Product Family Portable Lighting
 Series [130109](#)
 NEMA Configuration NEMA 5-15
 Outlet None
 Overview [Hand Lamps](#)
 Product Name Pro-Yellow®
 Type Hand Lamps
 UPC 78678863783
 Woodhead Yes

Physical

Cord Length - Primary N/A
 Cord Length - Secondary N/A
 Depth N/A
 Duty General
 Guard Included No
 Guard Type N/A
 Height N/A
 Length N/A
 Material - Guard Polycarbonate
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Fluorescent
 Lamp Type PL13/41
 Lamp Wattage - Maximum 13W
 Lumens 900
 On/Off Switch Yes
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number WT3F



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130109 Series](#)