

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202320062](#)
Status: **Active**
Overview: Brad® M23 Signal and Power Connectors
Description: Brad M23 Signal Connector, Male Contact Ø 1.0mm, Crimp Range 0.14-1.00mm²

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	120232
Comments	Male Contact 1.0mm
IP Rating	IP67
Material - Contact	Brass
Overview	Brad® M23 Signal and Power Connectors
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906301279

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	N/A
Material - Coupling Nut	N/A
Material - Plating Mating	Gold over Nickel
Orientation	Straight
Poles	N/A
Temperature Range - Operating	-40°C to +125°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	N/A

Material Info

Engineering Number	KCS06-01
--------------------	----------

Reference - Drawing Numbers

Sales Drawing	SD-120232-062
---------------	---------------

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[120232 Series](#)