

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1120360039](#)  
**Status:** **Active**  
**Overview:** [Brad® Ethernet Switches](#)  
**Description:** Direct-Link® Series 300 Managed Ethernet Switch, 5-Port RJ45, IP30

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Switches
Series	<a href="#">112036</a>
Approvals	CE, CUL, UL certified
Comments	10/100 Base TX (Mbaud)
IP Rating	IP30
MAC Address	2048
Overview	<a href="#">Brad® Ethernet Switches</a>
Product Literature Order No	987650-5531
Product Name	Direct-Link®
Protocol	EtherNet (IEEE 802.3)
Switch Functionality	Managed
Type	N/A
UPC	78172516107
Woodhead	Yes
<b>Physical</b>	
Ethernet Connector	N/A
Housing Width	27.18mm
Mechanical Shock	N/A
Mounting Style	DIN Rail, Panel Slots
Packaging Type	Carton
Ports	5
Power Input	None
Temperature Range - Operating	-40°C to +85°C
Uplink Connection	RJ45
Vibration	IEC 60068-2-27, IEC 60068-2-32, IEC 60068-2-6
<b>Electrical</b>	
Current - Maximum Output	0.5A
EMC	CE, EN 610006-2-4, FCC Part 15, ICES-003
Supply Voltage	10-30V DC
<b>Material Info</b>	
Engineering Number	DRL-350M
<b>Reference - Drawing Numbers</b>	
Sales Drawing	SD-112036-0010-001



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[112036 Series](#)