

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130105-0028](#)
Status: **Active**
Overview: Specialty Lighting
Description: Super-Safeway™ Rubber Hand Lamp 75W with LOVOLT® In-line Transformer Screw Release Guard, Cord Type 14/2 SOOW, 7.62m (25.0') Cord Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

General

Product Family	Portable Lighting
Series	130105
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	Specialty Lighting
Product Literature Order No	987650-8052
Product Name	Super-Safeway™
Type	Specialty Light
UPC	78678862500
Woodhead	Yes

Physical

Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	7.62m (25.0')
Depth	101.60mm (4.000")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	374.65mm (14.750")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Cord Type - Secondary	14/2 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	75W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC

Material Info

Old Part Number	1600-12A
-----------------	----------



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130105Series