

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130138-0082](#)
Status: **Active**
Overview: [Watertite® Wet-Location Wiring Solutions](#)
Description: Watertite® Multiple Outlet Pendant Box, GFCI, (1)NEMA 5-20 Duplex with Flip Lids, 4.57m (15.0') Cord Length, 12/3 SOOW Cord, Double Eye Wire Mesh Support Grip

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

General

Product Family	Power Distribution
Series	130138
Enclosure Rating	NEMA 4
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	No
Overview	Watertite® Wet-Location Wiring Solutions
Product Literature Order No	987650-7737
Product Name	Watertite®
Receptacle Type	Duplex
Type	Multiple Outlet Box
UPC	78678828312
Woodhead	Yes

Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	4.57m (15.0')
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Net Weight	285.760/kg
Number of Receptacles	1
Packaging Type	Carton

Electrical

Cord Type	12/3 SOOW
Current - Maximum per Contact	20A
GFCI	Yes
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-20
Voltage - Maximum	120V

Material Info

Old Part Number	70W33M123GF
-----------------	-------------



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130138Series