



Accessory Products

Closure caps for receptacles, connectors and Multi-ports
 Threaded unions for mating (2) cordsets
 Female and male plugs for liquid tight conduit terminations
 90° adapters with (1) male and (1) female plug

CLOSURE CAPS & THREADED UNIONS					
DESCRIPTION	FOR USE WITH	FIG	2P to 6P (A size)	6P (B size) to 8P	9P to 12P
ALUMINUM CLOSURE CAP WITH INTERNAL THREADS	MALE & FEMALE RECEPTACLES + MULTIPORT BASE UNITS	1	65-0086	65-0103	65-0105
ALUMINUM CLOSURE CAP WITH EXTERNAL THREADS	MALE & FEMALE CONNECTORS	2	65-0085	65-0102	65-0104
ALUMINUM THREADED UNION	MALE & FEMALE CONNECTORS	3	55-0426	55-0466	55-0496

MINI-CHANGE® PLUGS WITH #16 AWG PVC LEADS 6'-0" LONG FOR 1/2" LIQUID TIGHT CONDUIT					
		2P	3P	4P	5P
FEMALE FACE VIEW					
COLOR CODE		1- white 2- black	1- green-gnd 2- black 3- white	1- black 2- white 3- red 4- green-gnd	1- white 2- red 3- green-gnd 4- orange 5- black
FEMALE	FIG 4	40718	40925	41132	41344
MALE	FIG 4	40780	41037	51149	41593

90° ADAPTERS WITH (1) MALE PLUG AND (1) FEMALE PLUG					
		2P	3P	4P	5P
90°	FIG 5	40761	41048	41212	41481

Specifications



MECHANICAL	
CLOSURE CAPS W/ INTERNAL THREADS:	GRAY ANODIZED ALUMINUM
CLOSURE CAPS W/ EXTERNAL THREADS:	BLACK ANODIZED ALUMINUM
THREADED UNION:	GRAY ANODIZED ALUMINUM
LIQUID-TIGHT PLUGS	
CONNECTOR BODY:	ZINC PLATED STEEL
COUPLING NUT:	GRAY ANODIZED ALUMINUM
CLAMP NUT:	ZINC PLATED STEEL
INSERT:	PVC - UL STD 94 - V0
90° ADAPTER CONNECTOR BODY:	YELLOW NYLON
COUPLING NUTS:	ZINC DIECAST W/ BLACK EPOXY
INSERT:	PVC - UL STD 94 - V0
ELECTRICAL	
LIQUID-TIGHT PLUGS AND 90° ADAPTORS	
VOLTAGE RATING:	600V
	CURRENT: 2P - 13A
	3P - 10A
	4P - 8A
	5P - 8A
ENVIRONMENTAL	
PROTECTION:	IP65, NEMA 4
AMBIENT OPERATING TEMP:	-4° TO 221° F (-20° TO 105° C)
CERTIFICATIONS	
UL:	UL RECOGNIZED, FILE NO. E46237
CSA:	CSA CERTIFIED, FILE NO. LR6837

ACCESSORY DIMENSIONS & DETAILS

