

Home: >

Part Number: 130050-0381

ENET MMJ IND/RJ45 568A SHD 10M

Image not available

Status: Active
Series: [130050](#)
Category: Molex Parts
Engineering/Old PN: ENS2135M100

[CHECK DISTRIBUTOR INVENTORY](#)

[Add to My Parts](#)

Go to [Part Detail](#)▼

Series image - Reference only

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

Questions on Product Environmental Compliance? Email ProductCompliance@molex.com

Request Molex's CMRT from conflictminerals@molex.com

- EU ELV:**Not Reviewed
- EU RoHS:**Not Reviewed
- EU RoHS Phthalates:**Not Reviewed
- China RoHS:**Not Reviewed
- REACH SVHC:**Not Reviewed
- Low-Halogen Status:**Not Reviewed

[Product Compliance Statement](#)

Application Tooling

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

[VIEW ALL](#)

▶ ▶ **General**

▶ ▶ **Material Info**

PRODUCTS

- Antennas
- Application Tooling
- Cable Assemblies
- Connected Lighting
- Connectors
- Copper Flex
- Electrical Products
- Industrial Automation
- Membrane Switches
- Optical Solutions
- PCB Assemblies


QUICK LINKS

- Company Information
- Contact Molex
- Cross-Reference
- Koch Industries
- Industries
- Literature
- Molex Racing
- Press Room / Press Releases
- Product Index
- Sitemap

RESOURCES

- Supply Chain Transparency
- Compliance
- ecocare
- Feedback | Help
- Jobs
- Legal | Trademarks
- Mobile Site
- Supplier Portal
- Privacy Policy
- Tradeshows

STAY CONNECTED



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2017