

×

- [Products](#)
- [Industry Solutions](#)
- [CAREERS](#)
- [Resources](#)

- [Find Distributor](#)
- [Contact Molex](#)

Enter Part No. or Keyw

Search



[Product Name Index](#)



[Cross Reference](#)



Part Number: 130050-0287

ENET MMJ IND/IND 10T SHLD 4M

Image not available

Series image - Reference only

Status: Active

Series: [130050](#)

Category: Molex Parts

Engineering/Old PN: ENS1115M040

Product Environmental Compliance

[EU ELV](#):Not Reviewed

[EU RoHS](#):Not Reviewed

[EU RoHS Phthalates](#):Not Reviewed

[China RoHS](#):Not Reviewed

[REACH SVHC](#):Not Reviewed

[Low-Halogen Status](#):Not Reviewed

Part Detail

General

Status **Active**

Category Molex Parts

Series [130050](#)

UPC 78678844375

Material Info

Engineering Number ENS1115M040

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Products+

- [Product Categories](#)
- [Product Index](#)
- [Industries](#)

Quick Links+

- [Company Information](#)
- [Contact Molex](#)
- [Cross-Reference](#)
- [Koch Industries](#)
- [Investor Relations](#)
- [Literature](#)
- [Press Room / Press Releases](#)
- [Sitemap](#)
- [Terms & Conditions](#)

Resources+

- [Supply Chain Transparency](#)
- [Business Continuity](#)
- [Compliance](#)
- [ecocare](#)
- [Feedback | Help](#)
- [Jobs](#)
- [Legal | Trademarks](#)
- [Supplier Portal](#)
- [Privacy Policy](#)
- [Tradeshows](#)

Stay Connected



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2018