

# Literature APPLICATION Guide

## Panel Lights



### KEY FEATURES:

- State-of-the-Art Brilliant LED's
- 6mm to 22mm Sizes Available
- 2 Volts up to 380 Volts
- Red, Green, Yellow, Blue, or White Color Options
- Snap-in or Nut Mounting Options
- Various Termination Options: Wires, PC Pins, Quick Connect, or Solder Lugs
- Various Body Styles (IP-50 to IP-65)
- CUL Approved Models Available

### SPECIFICATIONS:

**Panel Hole Sizes:** 6mm, 8mm, 10mm, 12mm, 16mm, or 22mm

**Lens Color:** Same as LED Color

**LED Colors:** Red, Green, Yellow, Blue, White

**Rated Voltage:** 2V, 3V, 6V, 12V, 24V, 36V, 48V, 110V, 220V, or 380V

**LED Current:** 15 - 20 mA Max (see data sheet)

**Mounting Options:** Snap-in or Threads & Nut (see data sheet)

**Termination:** Wires, PC Pins, Solder Lugs, or Flat Blades (see data sheet)

**IP Ratings:** IP-50 to IP65 (see data sheet)

Call 317-612-1000 or Visit [www.mallory-sonalert.com](http://www.mallory-sonalert.com) for More Details