



HEAT SHRINK TUBING MWTM

MEDIUM-WALL LOW VOLTAGE INSULATION AND CORE PROTECTION TUBING UP TO MEDIUM VOLTAGE

KEY FEATURES

- High electrical characteristics and mechanical strength for low voltage applications
- Medium-wall, cross-linked polyolefin. UV stabilized against irradiation and weathering
- Halogen and silicon-free material content, non-corrosive, non-toxic, free of lead and aluminium
- Available inline coated with hot melt adhesive or uncoated
- Color black, 3:1 shrink ratio
- Unlimited shelf-life

TE Connectivity's (TE) Raychem MWTM heat shrink medium-wall tubing is designed for insulation on low voltage cable accessories, as well as for sealing and protection purposes on low and medium voltage cables and cable accessories. In this tubing type, the electrical and physical properties of cable oversheath and core insulation of low voltage cables are combined with ruggedness and easy installation.

During heating, TE's Raychem MWTM tubing shrinks to the original smaller diameter, fitting tightly over a wide range of cable sizes and cable accessories. At the same time the tubing's inner sealant wall gives a reliable moisture seal over even the most irregular shapes.

The MWTM tubing is widely used to insulate, protect and seal low voltage power cable joints and terminations, as well many further applications in cable accessories and electrical connections.

The material content of the MWTM tubing is halogen-free and stabilized against UV irradiation. The MWTM tubing is available, both uncoated or coated with hot-melt sealant. It has proven its long-term reliability in harsh climatic conditions and in polluted environments and has an unlimited shelf-life when stored under normal conditions.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.

Heat Shrink Tubing MWTM



Compliant to RoHS and REACH regulations.

Approved for offshore applications.

TESTING		
Physical Characteristic	Test Method	Material Requirements
Tensile Strength	ISO 37	14 MPa min
Ultimate Elongation	ISO 37	350% min
Hardness	ISO 868	≥ 45 shore D
Accelerated ageing 7 days at 150°C ± 2°C Tensile Strength Ultimate Elongation	ISO 188 ISO 37 ISO 37	14 MPa min 350% min
Thermal Endurance*	IEC 60216	120°C min.
Low Temperature Flexibility	ASTM D2671 Procedure C	No cracking at 4 hours at -40°C ± 3°C
Dielectric Strength	IEC 60243 part 1 and 2	≥ 10 kV/mm min.
Volume Resistivity	IEC 60093	1 x 10 ¹⁰ Ω cm min
Water Absorption	ISO 62 method 1	≤ 0.25% max after 14 days at 23°C ± 2°C
Weathering	The material from which MWTM is manufactured contains carbon black to protect it from ultra-violet light	
Additional Properties	Further details are given in TE's Raychem Specifications PPS 3010/19 (A) [1326].	
Resistance to Liquids		
7 days in transformer oil VDE 0370 at 23°C ± 2°C	ISO 1817	
Tensile Strength	ISO 37	14 MPa min
Ultimate Elongation	ISO 37	300% min.

PRODUCT SELECTION INFORMATION - DIMENSIONS ARE SHOWN IN MM						
Description	Application Range		Diameter		Wall Thickness	
	from	to	Expanded min	Recovered max	Expanded nom	Recovered min
MWTM- 10/3	3.5	9.0	10	3	0.3	1.0
MWTM- 16/5	5.5	14.5	16	5	0.3	1.4
MWTM- 25/8	9.0	22.5	25	8	0.4	2.0
MWTM- 35/12	13.0	31.5	35	12	0.4	2.0
MWTM- 50/16	18	45	50	16	0.5	2.0
MWTM- 63/19	21	57	63	19	0.6	2.4
MWTM- 75/22	24	68	75	22	0.6	2.7
MWTM- 85/25	28	77	85	25	0.6	2.8
MWTM- 95/29	32	86	95	29	0.7	3.1
MWTM- 115/34	37	104	115	34	0.7	3.1
MWTM- 140/42	46	126	140	42	0.7	3.1
MWTM- 160/50	55	144	160	50	0.7	3.2
MWTM- 180/60	66	162	180	60	0.7	3.2
MWTM- 245/80 *	88	220	245	80	n.a.	2.4
MWTM- 285/135 *	149	255	285	135	n.a.	1.4

* Uncoated only.

Standard Lengths: All sizes are available in the standard lengths 1000 mm and 1500 mm.
On request, other lengths and on spools. All lengths subject to standard cutting tolerances.

te.com/energy

© 2018 TE Connectivity. All Rights Reserved. EPP-2731-10/18-EN

Raychem, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and Company names mentioned herein may be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this brochure are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION: TE Technical Support Centers

USA:	+ 1 800 327 6996
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 896 089 903
Spain:	+ 34 916 630 400
Italy:	+ 39 333 250 0915
Benelux:	+32 16 508 695
Russia:	+7 495-790 790 2-200
China:	+ 86 (0) 400-820-6015