

Electrical Specifications

| | |
|------------------------|------------|
| Impedance | 50 OHM |
| Frequency Range | DC - 6 GHz |

Mechanical Specifications

| | |
|--------------------------|------------------|
| Durability | 500 Cycles Min |
| Mount | Cable |
| Cable Size | RG-178 |
| Temperature Range | -65° C to 165° C |
| Mating | Snap On |



[Click:
To Request A Quote
To Check Distributor's Inventory
For More Non-Magnetic Information](#)

Material Specifications

| | |
|---------------------------|---|
| Body | Brass |
| Outer/Center | Brass |
| Contacts Insulator | PTFE |
| Ferrule | Copper Alloy |
| Finish | 3 Min Gold Microninch Over 50 Microninch Copper |

Mechanical Dimensions

All dimensions are in millimeters

