

## Electrical Specifications

<b>Impedance</b>	50 OHM
<b>Frequency Range</b>	DC - 6 GHz

## Mechanical Specifications

<b>Durability</b>	500 Cycles Min
<b>Mount</b>	Surface
<b>Temperature Range</b>	-65° C to 165° C
<b>Mating</b>	Snap On

## Material Specifications

<b>Body</b>	Brass
<b>Outer/Center</b>	Brass
<b>Contacts Insulator</b>	PTFE
<b>Ferrule</b>	Brass
<b>Finish</b>	3 Min Gold Microninch Over 50 Microninch Copper



[Click:  
To Request A Quote  
To Check Distributor's Inventory  
For More Non-Magnetic Information](#)

## Mechanical Dimensions

All dimensions are in millimeters

