

## Electrical Specifications

<b>Impedance</b>	50 OHM
<b>Frequency Range</b>	DC - 3 GHz

## Mechanical Specifications

<b>Durability</b>	500 Cycles Min
<b>Mount</b>	Cable
<b>Cable Size</b>	RG-178
<b>Temperature Range</b>	-65° C to 165° C
<b>Mating</b>	Snap On



[Click:](#)  
[To Request A Quote](#)  
[To Check Distributor's Inventory](#)  
[For More Non-Magnetic Information](#)

## Material Specifications

<b>Body</b>	Brass
<b>Outer/Center</b>	Brass
<b>Contacts Insulator</b>	PTFE
<b>Ferrule</b>	Brass
<b>Finish</b>	3 Min Gold Microninch Over 50 Microninch Copper

## Mechanical Dimensions

All dimensions are in millimeters

