

TRIPP LITE USB-C

QUICK REFERENCE GUIDE



Today's laptops, tablets and smartphones are thinner and lighter than ever. The tradeoff is that many of these sleek devices have only a single USB-C port. Tripp Lite's adapters, hubs and docking stations help give that one connector a multitude of functions:

- Connect to virtually any display
- Gain USB-A ports for connecting to peripherals
- Read SD or Micro SD memory cards
- Connect stereo speakers
- Get fast Power Delivery (PD) charging
- Connect to the Internet when a Wi-Fi signal is weak or unavailable
- Transfer data at up to USB 3.1 Gen 2 speeds (10 Gbps)

DOCKING STATIONS & MULTIPOINT ADAPTERS

Expand functionality by adding connections to tablets and laptops, including A/V, Ethernet and card reader ports.

- Models include ports for DVI, VGA, DisplayPort, HDMI, USB-A, Ethernet, audio and memory card readers
- HD or UHD (4K) video output, with or without audio
- DP Alt Mode allows a compatible device to output HD or UHD via USB-C
- Models include USB-C power delivery (PD) port



Tripp Lite offers hundreds of solutions to make the most of any device's USB-C ports. In addition to docking stations and multiport adapters, take advantage of hubs to link multiple devices to a single port, and cables to transfer video and data at speeds faster than ever before.



Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.

For more information, contact:

Tripp Lite Pre-Sales Support

773.869.1236 | solutions@tripplite.com



Powering and Connecting
Your World

SEE REVERSE FOR PRODUCT OFFERING AND FEATURE MATRIX.

Model	Color	DISPLAYS												NUMBER OF DATA PORTS				PD CHARGING		STORAGE			Gb Ethernet	Audio Port	BC 1.2
		# of Displays*	Extended Mode**	Mirror Mode	Supports HDCP	HDMI	Resolution	MDP	DP	Resolution	DVI	Resolution	VGA	Resolution	USB 3.0 Gen 1 -A	USB 3.0 Gen 2 -A	USB 2.0 -A	USB-C Gen 1	Version	Wattage	SD	Micro SD			
U444-06N-HGUB-C	Black	1			✓	1	1080p							1				2.0	60			✓			
U444-06N-HGU-C	White	1			✓	1	1080p							1				2.0	60			✓			
U444-06N-HGUB-C	Black	1			✓	1	1080p							1				2.0	60			✓		✓	
U444-06N-HGU-C	White	1			✓	1	1080p							1				2.0	60			✓		✓	
U444-06N-HU-C	White	1			✓	1	1080p							1				2.0	60					✓	
U444-CAT-H	Black	1			✓	1	1080p																		
U444-06N-HDV4K	White	1			✓	1	4K30			1	1080p	1	1920 x 1200												
U444-06N-HDV4KB	Black	1			✓	1	4K30			1	1080p	1	1920 x 1200												
U442-DOCK11-S	Silver	1			✓	1	4K30											2.0	60	1	1	2	✓		
U444-06N-H4GUBC	Black	1			✓	1	4K30							1				2.0	60				✓	✓	
U444-06N-H4GU-C	White	1			✓	1	4K30							1				2.0	60				✓	✓	
U444-06N-H4UB-C	Black	1			✓	1	4K30							1				2.0	60						
U444-06N-H4U-C	White	1			✓	1	4K30							1				2.0	60					✓	
U442-DOCK10-S	Silver	1			✓	1	4K30							2				3.0	60		1				
U442-DOCK3-B	Black	1			✓	1	4K30				1	1920 x 1200		2			1	3.0	100	1	1	1	✓	✓	
U442-DOCK5D-GY	Gray	1			✓	1	4K30							3				3.0	100	1	1	2	✓	✓	
U442-DOCK5-GY	Gray	1			✓	1	4K30							3			1	3.0	100	1	1	2	✓	✓	
U444-06N-H3U-C	Gray	1			✓	1	4K30							3				3.0	100						
U444-06N-H4GUSC	Gray	1			✓	1	4K30							1				3.0	100				✓	✓	
U444-T6N-H4GUBC	Black	1			✓	1	4K30							1				3.0	100				✓	✓	
U444-T6N-H4UBC	Black	1			✓	1	4K30							1				3.0	100						
U442-DOCK13-S	Silver	1			✓	1	4K30							1			1						✓		
U444-06N-HV4GU	White	1			✓	1	4K30				1	1920 x 1200		1									✓		
U444-06N-HV4GUB	Black	1			✓	1	4K30				1	1920 x 1200		1									✓		
U444-06N-HV4K	White	1			✓	1	4K30				1	1920 x 1200													
U444-06N-H4UBC2	Black	1			✓	1	4K60							1				3.0	100						
U444-06N-DGUB-C	Black	1			✓					1	1080p			1				2.0	60				✓	✓	
U444-06N-DGU-C	White	1			✓					1	1080p			1				2.0	60				✓	✓	
U444-06N-DUB-C	Black	1			✓					1	1080p			1				2.0	60						
U444-06N-DU-C	White	1			✓					1	1080p			1				2.0	60						
U444-06N-VGUB-C	Black	1									1	1920 x 1200		1				2.0	60				✓	✓	
U444-06N-VGU-C	White	1									1	1920 x 1200		1				2.0	60				✓	✓	
U444-06N-VUB-C	Black	1									1	1920 x 1200		1				2.0	60						
U444-06N-VU-C	White	1									1	1920 x 1200		1				2.0	60						
U444-T6N-VUBC	Black	1									1	1920 x 1200		1				3.0	100						
U442-DOCK2-S	Silver	2	✓	✓	✓	1	4K30	1	4K30		1	1920 x 1200		3				2.0	60	1	1	1	✓	1	✓
U442-DOCK1	Silver	2	✓	✓	✓	1	4K30	1	4K30		1	1920 x 1200		3				2.0	60	1	1	1	✓	1	✓
U442-DOCK1-B	Black	2	✓	✓	✓	1	4K30	1	4K30		1	1920 x 1200		3				2.0	60	1	1	1	✓	1	✓
U442-DOCK4-S	Silver	2	✓	✓	✓	1	4K30		1	4K30		1	1920 x 1200	2		2	1	2.0	100				✓	2	✓
U442-DOCK6-GY	Gray	2		✓	✓	1	4K30				1	1920 x 1200		2			1	3.0	100				✓		✓
U444-06N-2H-MST	Gray	2	✓		✓	1	4K30																		
U442-DOCK12-S	Silver	2		✓	✓	2	1080p				1	1920 x 1200		1				2.0	60						
U442-DOCK7D-B	Silver	3	✓	✓	✓	1	4K30		1	4K30		1	1920 x 1200	3	2	2	1	3.0	100	1	1	2	✓	1	✓
U444-06N-HVDPW	White	3	✓		✓	1	4K30		1	4K60		1	1920 x 1200												
U460-002-2AM-C	White													2				2.0	60	1	1	2			✓