

Connecting the Classroom with Tripp Lite



Technology is quickly transforming traditional K-12 classrooms into network environments. Tripp Lite offers robust IT solutions to support school districts and educators at all levels as they strive to engage students with modern, interactive learning tools while keeping expenditures under control.

Charging, Syncing & Securing Mobile Devices

A Charging Stations & Carts

Protect your school's financial investment and simplify the use of mobile learning tools in the classroom.

- Locking steel enclosures deter theft during charging and storage.
- Instructors can easily update devices with wired syncing (USB models) or take advantage of compatibility with wireless syncing.
- Cable management promotes organization of devices and cords.
- Carts make it simple to move groups of devices from room to room.
- Desktop stations offer a compact option for charging and securing tablets.

Sharing Your Message

B Cables, Connectivity Solutions & USB Solutions

Connect devices to a Gigabit Ethernet network or show HD video on a large display. Use adapters to integrate new tech, like USB-C enabled laptops, with existing setups, reducing the need for costly upgrades.

C Display Mounts & Mobile Stands

Mount HDTVs or monitors on a wall to optimize viewing angles, plus move displays from room to room with new mobile floor stands.

D Keyspan® Presentation Remotes

Control presentation software from anywhere in the room with a wireless remote. Simple, intuitive operation keeps the focus on the lesson plan.

Protecting Equipment

E Desktop UPS Systems

In the case of a blackout, UPS systems provide enough time for instructors to perform an orderly shutdown of computers, saving data that might otherwise be lost.

F Surge Protectors

Keep equipment safe from power surges and reduce line noise (EMI/RFI) interference.

G Wall-Mount Racks

Save valuable floor space and keep equipment out of the way. Rack enclosures secure equipment in a locking cabinet to help prevent damage, tampering and theft.



◀ See Reverse for Top-Selling Tripp Lite Solutions for Connecting the Classroom

Powering and Connecting Your World

Top-Selling Tripp Lite Solutions for Connecting the Classroom

Many Products are E-Rate Eligible!

Sharing Your Message

Cables, Connectivity Solutions & USB Solutions

- Over 2,000 network, power, data and A/V solutions
- Many cables have a lifetime warranty

Cat6/5e Cables				
	5 ft.	10 ft.	15 ft.	25 ft.
Cat6 Gigabit Molded Patch Cables (Snagless)				
Black	N201-005-BK	N201-010-BK	N201-015-BK	N201-025-BK
Blue	N201-005-BL	N201-010-BL	N201-015-BL	N201-025-BL
Gray	N201-005-GY	N201-010-GY	N201-015-GY	N201-025-GY
Cat5e Molded Patch Cables (Also Available in Snagless)				
Blue	N002-005-BL	N002-010-BL	N002-015-BL	N002-025-BL
Gray	N002-005-GY	N002-010-GY	N002-015-GY	N002-025-GY

** 14 ft.

A/V Cables & Adapters	
Tripp Lite Model	Description
DVI	
P560-010	DVI Dual-Link Cable (M/M), 10 ft.
P561-010	DVI Single-Link Cable (M/M), 10 ft.
HDMI	
P566-006	HDMI to DVI Cable (M/M), 6 ft.
P568-006	High Speed HDMI Cable (M/M), 4K, 6 ft.
P568-050	HDMI Cable (M/M), 50 ft.
DisplayPort	
P580-006	DP Cable (M/M), 4K, 6 ft.
P580-010	DP Cable (M/M), 4K, 10 ft.
P582-006	DP to HDMI Cable (M/M), 6 ft.
P586-006-DVI	Mini DP to DVI Cable (M/M), 6 ft.
P586-006-HDMI	Mini DP to HDMI Cable (M/M), 6 ft.
P586-006-VGA	Mini DP to VGA Cable (M/M), 6 ft.
P137-06N-HDV	Mini DP to VGA/DVI/HDMI Adapter

Charging, Syncing & Securing Mobile Devices

Charging Stations & Carts

- Capacities for up to 48 USB or AC devices
- Desktop models accommodate up to 10 devices

Charging Stations		
Black Model	White Model	Capacity
USB Charging Stations		
CS16USB	CS16USBW	16 Tablets
CSC16USB*	—	16 Tablets
CS32USB	—	32 Tablets
CS48USB	CS48USBW	48 Tablets
AC Charging Stations		
CSC16AC*	CSC16ACW	16 Laptops/Chromebooks
CS16AC	—	16 Tablets
CS32AC	—	32 Tablets

*Optional cart conversion kit available.

Charging Carts		
Black Model	White Model	Capacity
USB Charging Carts		
CSC32USB	CSC32USBW	32 USB Devices
AC Charging Carts		
CSC32AC	CSC32ACW	32 Laptops/Chromebooks
CSC21AC	—	21 AC Devices
CSC27AC	—	27 AC Devices
AC Charging Cart with Zone Charging & New Features		
CSC36AC	—	36 AC Devices
CSC42AC	—	42 AC Devices
CSC45AC	—	45 AC Devices
CSC48AC	—	48 AC Devices

Desktop Charging Stations—For tablets and e-readers	
Tripp Lite Model	Description
CSD1006USB	10-Port USB Charging Station
CSD1006AC	10-Outlet AC Charging Station with Surge Protection

A/V Extenders	
Tripp Lite Model	Description
DVI over Cat5/Cat6 Extender Kits (Transmitter + Receiver)	
B140-101X	Extender, 200 ft. Range
B140-101X-U	Extender, USB Powered, 125 ft. Range
HDMI over Cat5/Cat6 Extender Kits (Transmitter + Receiver)	
B125-150	Extender, Dual Cat5/Cat6, 150 ft. Range
B126-1A1	Extender, 200 ft. Range
B150-1A1-HDMI	DP to HDMI Extender, 150 ft. Range
BHDBT-K-SI-ER	HDBaseT (HDMI) Extender, 500 ft. Range
VGA over Cat5/Cat6 Extender Kits (Transmitter + Receiver)	
B130-101-2	Extender, 1,000 ft. Range
B130-101-U	Extender, USB Powered, 500 ft. Range
B130-101A-SR	Extender with Audio, USB Powered, 300 ft. Range
B130-101A-2	Extender with Audio, 1,000 ft. Range

USB Solutions	
Tripp Lite Model	Description
USB Cables	
U022-006	USB 2.0 A/B Cable (M/M), 6 ft.
U050-006	USB 2.0 A to Micro-B Cable (M/M), 6 ft.
USB Hubs	
U222-004	4-Port USB 2.0 Ultra-Mini Hub, USB-A
U222-007-R	7-Port USB 2.0 Hub with Stand, USB-A
USB-C Hubs/Adapters	
U436-06N-G-C	USB-C to RJ45 Ethernet (M/F), PD, White
U442-DOCK1	USB-C to 4K HDMI, DVI, VGA, DP/mDP, USB-A, Ethernet, 3.5 mm, Card Reader, PD, Silver
U442-DOCK10-S	USB-C to 4K HDMI, USB-A, PD, Micro SD, Silver
U442-DOCK13-S	USB-C to 4K HDMI, USB-A, Ethernet, Silver
U444-06N-DVI-AM	USB-C to DVI (M/F), White
U444-06N-V-C	USB-C to VGA (M/F), PD, White
U444-06N-HV4GUB	USB-C to 4K HDMI, VGA, USB-A, Ethernet, Black

Protecting Equipment

Desktop UPS Systems

- Over 80 models to provide power protection and reliable battery backup
- Up to a 3-year warranty; up to \$250K insurance

Tripp Lite Model	Output Capacity	Outlets + Data Line Protection	Comm. Ports
Internet Office® Series			
INTERNET550U	550VA/300W	8 + Tel	USB
INTERNET750U	750VA/450W	12 + Tel	USB
AVR Series—Automatic Voltage Regulation (AVR)			
AVR550U	550VA/300W	8 + Tel	USB
AVR750U	750VA/450W	12 + Tel	USB
Digital Series—Automatic Voltage Regulation (AVR), LCD Screen			
OMNI900LCD	900VA/475W	8	USB
SMART1000LCDU	1000VA/500W	8 + Tel/Coaxial	USB
SMART1300LCDT	1300VA/720W	8 + Tel/Coaxial	USB
OMNI1500LCDT	1500VA/810W	10 + Tel/Ethernet/Coaxial	USB
SMART1500LCDT	1500VA/900W	10 + Tel/Ethernet/Coaxial	USB

Wall-Mount Racks

- Over 50 models from 2U to 26U; capacities up to 500 lb.
- 5-year warranty and most ship fully assembled

Tripp Lite Model	Size	Description	Capacity
SRWF2U	2U	Vertical-Mount	150 lb.
SRWF5U	5U	Vertical-Mount	150 lb.
SRW6U	6U	Non-Swinging	200 lb.
SRW9U	9U	Non-Swinging	200 lb.
SRW10US	10U	Swinging	200 lb.
SRW12US	12U	Swinging	200 lb.
SRW12USG	12U	Swinging, Clear Acrylic Window	200 lb.
SRW15US	15U	Swinging	200 lb.
SRW18US	18U	Swinging	250 lb.
SRW26US	26U	Swinging	250 lb.

Sync/Charge Cables				
	10 in.	3 ft.	6 ft.	10 ft.
USB-A to Lightning Cables (M/M)				
Black	M100-10N-BK	M100-003-BK	M100-006-BK	M100-010-BK
White	—	M100-003-WH	M100-006-WH	M100-010-WH

Display Mounts & Mobile Stands

- Over 50 models to mount displays, tablets and projectors
- Options for wall, desk and ceiling mounting

Tripp Lite Model	Description
DCPU1	CPU Mount
DDR0810TRI	Full-Motion Flexible Stand for 8 to 10 in. Tablets
DUNVPJT	Full-Motion Universal Ceiling Mount for Projectors
DWMSC3780MUL	Full-Motion Wall Mount for 37 to 80 in. Displays, Security Model
DWF2655X	Fixed Wall Mount for 26 to 55 in. Displays
DWT4585X	Tilt Wall Mount for 45 to 85 in. Displays
DWM60100XX	Swivel/Tilt Wall Mount for 60 to 100 in. Displays
DMCS3270XP	Mobile Floor Stand, 32 to 70 in. Displays
DMCS60100XX	Mobile Floor Stand, 60 to 100 in. Displays
WWSRC	Mobile Standing Desk on Wheels

Keyspan Presentation Remotes

- Feature long-range RF wireless technology
- Compatible with PowerPoint and Keynote

Tripp Lite Model	Description
PR-PRO3	100 ft. Range, Mouse & Audio Controls
PR-US2	60 ft. Range, Mouse & Multimedia Controls
PR-EZ1	60 ft. Range, Audio Controls

Surge Protectors

- Over 150 models to protect anything with a plug against voltage spikes and line noise
- Lifetime warranty; up to \$500K insurance

Tripp Lite Model	Joule Rating	Outlets + USB Charging Ports	Cord Length	Color
Isobar® Surge Protectors—Premium Protection				
ISOBAR4ULTRA	3330	4	6 ft.	Lt. Gray
ISOBAR6ULTRA	3330	6	6 ft.	Lt. Gray
ISOBAR8ULTRA	3840	8	12 ft.	Lt. Gray
Protect It!® Surge Protectors				
SK30USB	540	3 + 2 (2.1A Total)	Direct Plug-In	Black
TLP6B	360	6	6 ft.	Black
TLP606	790	6	6 ft.	Lt. Gray
TLP606B	790	6	6 ft.	Black
TLP606USB	990	6 + 2 (2.1A Total)	6 ft.	Lt. Gray
TLP606DMUSB	2100	6 + 2 (2.1A Total) + Mounting Clamp	6 ft.	Black
SWIVEL6	1500	6 (Pivoting)	Direct Plug-In	Black
TLP74R	1080	7 (6 Right-Angle)	4 ft.	Lt. Gray
SUPER7	2160	7	7 ft.	Lt. Gray
TLP712	1080	7	12 ft.	Lt. Gray
TLP712B	1080	7	12 ft.	Black
TLP825	1440	8	25 ft.	Lt. Gray

To connect your classroom, contact
Tripp Lite Pre-Sales Tech Support:

773.869.1236 | solutions@tripplite.com



Powering and Connecting Your World