

### **DEUTSCH**

TE Internal #: DTT-16-01

TE Internal Description: CRIMP TOOL

View on TE.com >



Application Tooling > Hand Crimping Tools



Tool Grade: Commercial Crimp Tooling

Ratchet Configuration: Operator Releasable & Adjustable

Die Sets Type: Fixed In Tool

TE Certification: Cannot be Certified
Power Technology Type: Manual

## **Features**

### **Contact Features**

Contact Size

Other	
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Fixed In Tool
TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	Straight Action Hand Tool

Size 16

# **Product Compliance**

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



#### Free

## Solder Process Capability

Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


# Customers Also Bought



TE Part #160922-2 FF 110 REC 0.2-0.5MM2 TPBR



TE Part #1801178-1
3W RECEPTACLE HP CONNECTOR
BLACK



TE Part #HDC9-JDL082397 DUST CAP, 9P, REC, BLK, LANYARD, HD10






TE Part #K1143723 Relay 29-014-12-941











### **Documents**

Product Drawings
CRIMP TOOL



English

Datasheets & Catalog Pages

**Bottoming Dies** 

English

**Instruction Sheets** 

Instruction Sheet (U.S.)

English