



PRODUCT CHANGE NOTIFICATION (PCN)

ISSUE DATE: 25/4/2022
MODIFICATION / REVISION DATE: 25/4/2022

DK-1511-007/G MODULAR CABLE

CHANGE NOTIFICATION: PCN 20220425_DK-1511-007/G

DESCRIPTION OF CHANGES: CHANGE OF DATA SHEET
CHANGE OF DATA SHEET
New Draw.-No. ASS_7160_CAreV04

REASON FOR CHANGE: CHANGE OF PRODUCT LOCATION
CHANGE OF PRODUCT LOCATION

KEY CHARACTERISTICS OF CHANGE: Details see page 3

PRODUCTS AFFECTED: DK-1511-007/G

DATE OF CHANGE AND IMPLEMENTATION: CHANGE: WEEK 18 / YEAR 2022
IMPLEMENTATION: 25/4/2022

RESPONSE: NO RESPONSE TO THIS NOTIFICATION IS REQUIRED



Auf dem Schüffel 1
 D-58513 Lüdenscheid
 Tel.: +49-2351 - 554-200
 Fax: +49 (2351) 554-861
 info@assmann-wsw.com
 www.assmann-wsw.com

PRODUCT CHANGE NOTIFICATION (PCN)

ISSUE DATE: 25/4/2022
 MODIFICATION / REVISION DATE: 25/4/2022

DK-1511-007/G	OLD VERSION	DK-1511-007/G	NEW VERSION																				
<p>Appearance</p>		<p>Appearance</p>																					
<p>BOM</p> <p>SPECIFICATIONS:</p> <p>1. CONDUCTOR:</p> <p>1.1 CONDUCTORS: 24AWG 7*0.19±0.015mm</p> <p>1.2 CONDUCTOR INSULATION COLOR CODING: ONE WHITE/ORANGE, ONE ORANGE, ONE WHITE/GREEN, ONE GREEN, ONE BLUE, ONE WHITE/BLUE, ONE WHITE/BROWN, ONE BROWN.</p> <p>2. CABLE JACKET</p> <p>2.1 PRINTING ON THE JACKET: CM (UL) C(UL) 4P 24AWG UTP CAT.5E PATCH CABLE ISO/IEC 11801 & EN 50288 & ANSI/TIA-568-C.2</p> <p>3. CABLE ASSEMBLY</p> <p>3.1 SEE SECTION A-A FOR DIMENSIONS</p> <p>3.2 CABLE TIE: WHITE TIE</p> <p>3.3 WIRING TIE COLOR</p> <p>3.4 CONTACT PLUG: RJ45 8P8C 3u pc UL 94V-2</p> <p>4. CABLE JACKET COLOR: ACCORDING TO CUSTOMER'S REQUEST</p>		<p>BOM</p> <table border="1"> <tbody> <tr> <td>④</td> <td></td> <td>Molding PVC</td> <td>2</td> <td>Molding PVC 65P</td> </tr> <tr> <td>④</td> <td></td> <td>RJ45 CONN</td> <td>2</td> <td>RJ45 8P8C, contacts 3u" gold-plated Un-shielded PC UL94V-2</td> </tr> <tr> <td>④</td> <td></td> <td>CABLE</td> <td>1</td> <td>CAT 5E U/UTP(24AWGx1PR)*4+PVC Jacket OD:5.2±0.3mm</td> </tr> <tr> <th>NO.</th> <th></th> <th>NAME</th> <th>Q'TY</th> <th>SPECIFICATION</th> </tr> </tbody> </table>		④		Molding PVC	2	Molding PVC 65P	④		RJ45 CONN	2	RJ45 8P8C, contacts 3u" gold-plated Un-shielded PC UL94V-2	④		CABLE	1	CAT 5E U/UTP(24AWGx1PR)*4+PVC Jacket OD:5.2±0.3mm	NO.		NAME	Q'TY	SPECIFICATION
④		Molding PVC	2	Molding PVC 65P																			
④		RJ45 CONN	2	RJ45 8P8C, contacts 3u" gold-plated Un-shielded PC UL94V-2																			
④		CABLE	1	CAT 5E U/UTP(24AWGx1PR)*4+PVC Jacket OD:5.2±0.3mm																			
NO.		NAME	Q'TY	SPECIFICATION																			
<p>FOR DETAIL, PLEASE TAKE ATTACHED NEW DRAWING: FOR REFERENCE</p>																							


PCN REVISION HISTORY:

DATE OF REVISION: 25/4/2022

REVISION NUMBER: 00

page 3/

1 2 3 4 5 6 7



Order code: **DK-1511-XXX/XX**


color: **BL(black), WH(white), B(blue), G(grey)**

Length: see table ①

PIN OUT

CN1	WIRE COLOR	CN2
1	ORANGE/WHITE	1
2	ORANGE	2
3	GREEN/WHITE	3
6	GREEN	6
4	BLUE	4
5	BLUE/WHITE	5
7	BROWN/WHITE	7
8	BROWN	8

① Length	Feet	mm	tolerance (mm) ③
001	1	305	+30.5/-15.3
003	3	914	+45.8/-36.6
005	5	1524	±45.8
007	7	2134	±64.1
010	10	3048	±91.5
015	15	4572	±137.3
020	20	6096	±183
025	25	7620	±228.8
050	50	15240	±457.5
100	100	30480	±915



Electrical
 Open/short/intermittence: 100%
 Dielectric strength: 2.5KV DC-2seconds.
 The operating temperature: -20°C~+60°C

④		Molding PVC	2	Molding PVC 65P
④		RJ45 CONN	2	RJ45 8P8C, contacts 3u" gold-plated Un-shielded PC UL94V-2
④		CABLE	1	CAT 5E U/UTP(24AWGx1PR)*4+PVC Jacket OD:5.2±0.3mm
NO.	NAME.	SPECIFICATION		

Scale	Free					Date	Name	Customer-No.
TOLERANCE		④	Change the plant	12.04.2022	Luca	Drawn	24.06.2014	Joanna
X.	±X	③	Add tolerance for cable length	20.09.2019	Amy	Approved	12.04.2022	Luca
X.XX		②	Add new length version	06.04.2017	Amy			
X.XX		①	Update length version	07.12.2016	Amy			
DIM	TOL	①	Update length version	07.12.2016	Amy			
X.°		①	Drawn	24.06.2014	Joanna			ASSMANN WSW-No. DK-1511-XXX/XX
								Drawing-No. ASS 7160 CA
Angle	TOL	Id.	Modification	Date	Name	Replace		SHEET

1 2 3 4 5 6 7