


T-3 1/4 Miniature Bayonet Base



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
CM49	2.00	.06	.04	1,000	S-2
CM1809	2.00	.06	.02	1,000	C-6
CM43	2.50	.50	.50	3,000	C-2R
CM45	3.20	.35	.50	3,000	C-2R
CM1490	3.20	.16	.20	3,000	C-2R
CM1688	3.75	.09	.18	1,000	C-2R
CM1804	4.00	.06	.07	1,000	S-2
CM1867	4.00	.06	.06	2,000	C-6
CM1850	5.00	.09	.25	1,500	C-2R
CM1851	5.00	.12	.40	40	C-2R
CM1906	5.00	.07	.19	1,000	C-6
CM316	6.00	.70	3.40	500	C-2R
CM1689	6.00	.14	.35	2,000	C-2V
CM44	6.30	.25	.90	3,000	C-2R
CM47	6.30	.15	.50	3,000	C-2R
CM238	6.30	.50	2.00	2,000	C-2R
CM239	6.30	.36	.67	5,000	C-2R
CM240	6.30	.36	.67	5,000	C-2R
CM267	6.30	.15	.33	5,000	C-2R
CM755	6.30	.15	.33	20,000	C-2R
CM1302	6.30	.04	.08	5,000	C-6
CM1810	6.30	.40	1.40	3,000	C-2R
CM1847	6.30	.15	.38	5,000	C-2R
CM1866	6.30	.25	.65	5,000	C-2R
CM1888	7.00	.50	2.00	1,500	C-2R
CM1908	7.00	.19	.30	2,000	C-2R
CM1816	13.0	.33	3.00	1,000	C-2V
CM181	14.0	.41	3.00	1,500	C-2F
CM756	14.0	.08	.31	15,000	C-2F
CM1488	14.0	.15	1.50	200	C-2V
CM1815	14.0	.20	1.40	3,000	C-2V
CM1889	14.0	.27	2.00	1,500	C-2F
CM1891	14.0	.24	2.00	500	C-2F
CM1893	14.0	.33	2.00	7,500	C-2F
CM1894	14.0	.24	2.00	500	C-2V
CM1898	14.0	.24	2.00	7,500	2C-2R
CM216	14.4	.24	1.00	3,000	C-2F
CM1813	14.4	.10	.86	1,000	C-2V
CM1892	14.4	.12	.75	1,000	C-2F
CM1909	14.4	.10	.86	1,000	C-2V
CM1881	15.5	.24	2.20	500	C-2F