## Wire Management


## VK-Flex Molded Nylon Wiring Duct (Halogen Free)

Description: A flexible wiring duct that is especially suitable for switchgear, control panels, distribution equipment, cubicles and other areas where flexibility of design and installation are required.

The one-piece design with its overlapping fingers, eliminates the separate cover used with conventional duct, makes rewiring easy and lends itself to a more efficient use of space. Open slots allow for lead-offs and because the duct is molded, there are no sharp edges.

Each strip is fully interlocking for continuous end-to-end attachment. Molded with slotted mounting holes, VK-FLEX is also available with a permanent, self-adhesive backing - eliminating the need for other types of fasteners.


The open design of VK-FLEX, allowing for air circulation along with a temperature operating range of -40°C to 100°C (-40°F to 212°F), makes it especially suitable for enclosed areas where heat build-up may be a problem.




## **Specifications**

Material: Polyamide UL94V-O
Color: Standard color is Gray

Mounting Slots	Permanent	Dimensions						Wire Capacity			Std.
Catalog Number	Self-Adhesive Strip Catalog Number	<b>w</b> (i	nches)	L	w	(mm)	L	#18	#16	#14	Pkg. lengths
24 400 0040 0	24 400 0040 4	0.42	0.50	0.04	44	4.5	250	40	0	-	40
34.188.0010.0	34.188.0010.1	0.43	0.59	9.84	11	15	250	10	8	5	40
34.188.0020.0	34.188.0020.1	0.90	0.83	19.68	23	21	500	20	18	13	40
34.188.0030.0	34.188.0030.1	1.30	1.22	19.68	33	31	500	57	46	30	40
34.188.0040.0	34.188.0040.1	1.69	1.77	19.68	43	45	500	101	81	53	40



34.188.0010.0 &.1 side view



All other VK-FLEX side view

