

Single Contact Candelabra Bayonet

11 SERIES

UL Recognized

Maximum Rating: 25 Watts, 12 Volts

Electro-Tinned Plated Steel Shell

Grounded

6" Wire Lead

11-240XT

Plug button: zinc plated steel, for 15/16" hole with panel thickness range 1/32" to 5/64".

Grounded only.

11-245

Grounded only.

11-255

Grounded only.

11-260

Grounded only.

11-272

For reversed bracket:
Grounded unit: **11-271.**

Grounded only.

11-275

Grounded only.