



NE8MX-B-TOP

Cable connector carrier consists of a black chromium shell, chuck and boot. The boot is suitable for cable diameters from 5 - 8 mm. For non pre-assembled cables only. Cable connector carrier does not include a RJ45 plug.

IP65 rated and TOP approved in consideration to UL50E by mating with related cable or chassis connector of the XLR TOP range.



ATTENTION: Does not intermate with the CAT6 chassis connectors NE8FDY-C6 and NE8FDY-C6-B.



Features & Benefits

- The RJ45 system for harsh and demanding environment
- IP65 rated and TOP approved in consideration to UL50E by mating with related cable or chassis connector of the XLR TOP range
- Protects Ethernet connections in a variety of commercial type applications and is designed to prevent breakage of the fragile components of standard RJ45 connectors
- Cable connector carrier accepts the most common RJ45 plugs (see list at downloads)
- Rugged diecast shell and unique chuck type strain relief
- Allows assembly of non pre-assembled conventional RJ45 cables