

TRUE OUTDOOR PROTECTION


XLR TOP
powerCON® TRUE1® TOP
etherCON® TOP



NEUTRIK®

SETTING STANDARDS

Neutrik Headquarters in Schaan, Principality of Liechtenstein





NEUTRIK® – the premium brand of the Neutrik Group

Neutrik is the worldwide leading supplier of professional connectors and connector systems for the entertainment industry and other complex special applications.

Located in The Principality of Liechtenstein, in the middle of Europe, Neutrik is synonymous with the development, production and distribution of innovative products which have set the standards. No matter whether a rock band or a lighting designer, an industrial application, a broadcast studio or LED Display application – Neutrik offers a superior quality and reliable connector solution for every application.

STATE-OF-THE-ART MANUFACTURING

More than 1000 highly trained employees, modern production facilities and standardized workflows ensure superior quality. Since the start in 1975 Neutrik produced more than 1 billion connectors that have set standards in functionality, technical reliability and durability around the world.

Neutrik's management system and processes are certified according to ISO 9001 and comply to the environmental standards RoHS, REACH and Sony Green Partner.

TRUE OUTDOOR PROTECTION

Neutrik's new range of TRUE OUTDOOR PROTECTION products for demanding outdoor applications continues to set standards. Approved for outdoor use according UL50E. UV resistant and IP65 rated.



**TRUE
OUTDOOR
PROTECTION**

TRUE OUTDOOR PROTECTION

etherCON® TOP



powerCON® TRUE1® TOP



XLR TOP



**SETTING
STANDARDS**

TRUE OUTDOOR PROTECTION



TRUE OUTDOOR PROTECTION

The highly innovative entertainment industry is permanently evolving accompanied by increasing demands on interconnection systems. Particularly environmentally sealed connectors are highly requested for heavy-duty and harsh environment applications of entertainment equipment like PA systems, signs and LED screens or lightings.

Neutrik took up the challenge and developed a new line of TRUE OUTDOOR PROTECTION (TOP) products for demanding outdoor applications. This new range includes the popular powerCON TRUE1, etherCON and XLR series. These ruggedized sealed connectors feature not only IP protection but also UV resistance approved according to UL50E.



UV



IP

GLOBAL ENCLOSURE STANDARDS

For safety reasons, connectors have to be protected from outside influences like dust, foreign objects, moisture, water and sunlight. The most common and globally recognized standards for outdoor applications are IEC 60529 with the IPxx ingress protection levels and the UL50E / NEMA 250 enclosure type rating. Although these standards have the same goal to identify an enclosure capacity to withstand environmental influences, they differ in their definition, testing and pass criteria. The UL50E standard requires an UV test for thermoplastic materials which does not form part of the IP test. Neutrik have ensured that the new TOP range of products met both internationally recognized standards.

To ease equipment qualification Neutrik designed and qualified their TOP line to the connector standards IEC 61076-2-103, IEC 60320-1, UL 1977, UL 498. But in addition Neutrik took into account the special requirements for wet locations and outdoor applications and qualified the TOP line also according UL50E.

**SETTING
STANDARDS**



**TRUE
OUTDOOR
PROTECTION**

SETTING STANDARDS



NE8MX-TOP



NE8FDV-TOP

etherCON® TOP

ORDERING INFORMATION

NE8MX-TOP	Rugged RJ45 cable connector carrier
NE8FDV-TOP	Rugged D-size chassis connector
NE8FDP-TOP	Rugged D-size feedthrough
NE8FDH-C5E-TOP	Rugged D-size PCB mount
SE8FD-TOP	Outdoor assembly kit

- Heavy-duty sealed RJ45 system for harsh environment
- Rugged cable connector carrier accepting most common RJ45 plugs
- D-sized receptacles for PCB mount and IDC termination or as feedthrough adapter
- Outdoor protection acc. IP65 and UL50E
- Uses high impact UV resistant materials per UL
- Sealing when disconnected by attached cover
- Class D or CAT5e acc. ISO/IEC 11801 and TIA/EIA 568B





NAC3FX-W-TOP



NAC3MX-W-TOP



NAC3PX-TOP



NAC3MPX-TOP



NAC3FPX-TOP

powerCON® TRUE1® TOP

ORDERING INFORMATION

NAC3FX-W-TOP	Locking Power-In cable connector
NAC3MX-W-TOP	Locking Power-Out cable connector
NAC3PX-TOP	Appliance inlet-outlet combination
NAC3MPX-TOP	Appliance inlet connector
NAC3MPX-WOT-TOP	Appliance inlet connector, without insulation divider
NAC3FPX-TOP	Appliance outlet connector
NAC3FPX-ST-TOP	Appliance outlet connector, screw terminals
NAC3FPX-WOT-TOP	Appliance outlet connector, without insulation divider
SCNAC-PX	Rubber sealing cover for NAC3PX-TOP
SCNAC-MPX	Rubber sealing cover for NAC3MPX-TOP
SCNAC-FPX	Rubber sealing cover for NAC3FPX-TOP

- True mains connector with breaking capacity (CBC)
- Designed to be engaged and disengaged in normal use when live or under load
- Lockable 16A (acc. IEC, VDE) / 20A (acc. UL) connector
- Complete system with inlet and outlet connectors
- Outdoor protection acc. IP65 and UL50E enclosure type 4
- Uses high impact, UV resistant materials per UL
- Certified according IEC 60320-1 and UL 498



**TRUE
OUTDOOR
PROTECTION**

SETTING STANDARDS



NC3FX-TOP



NC3MDX-TOP



NC3MX-TOP



NC3FDX-TOP

XLR TOP

ORDERING INFORMATION

NC3FX-TOP	Heavy duty female 3 pole XLR cable connector
NC5FX-TOP	Heavy duty female 5 pole XLR cable connector
NC3MX-TOP	Heavy duty male 3 pole XLR cable connector
NC5MX-TOP	Heavy duty male 5 pole XLR cable connector
NC3FDX-TOP	Heavy duty, female 3-pole XLR chassis connector
NC5FDX-TOP	Heavy duty, female 5-pole XLR chassis connector
NC3MDX-TOP	Heavy duty, male 3-pole XLR chassis connector
NC5MDX-TOP	Heavy duty, male 5-pole XLR chassis connector
SCFDX-TOP	Sealing cover for NC3FDX-TOP
SCMDX-TOP	Sealing cover for NC3MDX-TOP

- Heavy-duty sealed XLR connector range
- 3 and 5 pin chassis and cable connector
- Outdoor protection acc. IP65 and UL50E
- Maintain sealing when in use and when disconnected
- Uses high impact UV resistant materials per UL
- Gold plated contacts
- Optional dust protection cap



**TRUE
OUTDOOR
PROTECTION**

**SUPERIOR
QUALITY**

**UNMATCHED
RELIABILITY**

**IP65
RATED**

**UV
RESISTANT**



LIECHTENSTEIN (HEADQUARTERS)

Neutrik AG, Im alten Riet 143,
9494 Schaan, Liechtenstein
T +423 237 24 24, F +423 232 53 93, neutrik@neutrik.com

CHINA

Ningbo Neutrik Trading Co., Ltd., Shiqi Street, Yinxian Road West
Fengjia Village, Hai Shu District, Ningbo, Zhejiang, 315153
T +86 574 88250833, sales@neutrik.com.cn

HONG KONG

Neutrik Hong Kong LTD., Suite 18,
7th Floor Shatin Galleria Fotan, Shatin
T +852 2687 6055, sales@neutrik.com.hk

USA

Neutrik USA Inc., 4115 Taggart Creek Road,
Charlotte, North Carolina, 28208
T +1 704 972 30 50, info@neutrikusa.com

GERMANY /NETHERLANDS /DENMARK /AUSTRIA

Neutrik Vertriebs GmbH, Felix-Wankel-Strasse 1,
85221 Dachau, Germany
T +49 8131 28 08 90, neutrik@neutrik.de

FRANCE

Neutrik® France, 52 Rue d'aguessseau,
92100 Boulogne
T +33 1 41 31 67 50, info@neutrik.fr

GREAT BRITAIN

Neutrik (UK) Ltd., Westridge Business Park, Cothey Way Ryde,
Isle of Wight PO33 1 QT
T +44 1983 811 441, sales@neutrik.co.uk

JAPAN

Neutrik Limited, Yusen-Higashinibashi-Ekimae Bldg., 3-7-19
Higashinibashi, Chuo-ku, Tokyo 103
T +81 3 3663 47 33, mail@neutrik.co.jp

INDIA

Neutrik India Pvt. Ltd., Level 3, Neo Vikram, New Link Road,
Above Audi Show Room, Andheri West, Mumbai, 400053
T +91 982 05 43 424, anklesaria@neutrik.com

ASSOCIATED COMPANIES

Contrik AG, Steinackerstrasse 35, 8902 Urdorf, Switzerland
T +41 44 736 50 10, contrik@contrik.ch

H. Adam GmbH, Felix-Wankel-Straße 1, 85221 Dachau, Germany
T +49 8131 28 08-0, anfrage@adam-gmbh.de

TOP Products – NF23-V4 – 201903 – Data subject to change without prior notice. © 2018 NEUTRIK®.
NEUTRIK®, powerCON®, etherCON® are registered trademarks of NEUTRIK AG. ALL RIGHTS RESERVED.



www.neutrik.com