



# R4E310 Series

Motorized Impeller

## Ø 310mm Backward Curved

- Backward curved centrifugal fans feature extremely long blades. These impellers are highly resistant to dirt and dust. Their hydraulic efficiency is very high.
- Impeller completely made of plastic PA 6.
- Maintenance-free ball bearings.
- Insulation class "B". Cable exit: variable. Direction of rotation is CW as seen from intake side.
- UL, CSA, VDE approvals on some models, please contact application engineering.
- Recommended inlet ring: 9621-2-4013.

Part Number	Curve	CFM @ 0	VAC	Hertz	Power (W)	dBA	Max Amb. Temp C	Bearing Type	Features	Capacitor (µF)	Wgt. (lbs)
R4E310-AE13-17	1	1265	115	60	155	68	60	Ball	Leads	12	8.00
R4E310-AE05-17	1	1265	230	50/60	165	68	60	Ball	Leads	4	8.00
R4E310-AE15-16	1	1265	277	60	155	68	60	Ball	Leads	3	8.00
R4E310-AE13-16	1	1265	115	60	155	68	60	Ball	Leads	12	8.00

