

Electrical Specifications

Impedance	50 OHM
Frequency Range	DC - 6 GHz

Mechanical Specifications

Durability	500 Cycles Min
Mount	Surface
Temperature Range	-65° C to 165° C
Mating	Snap On

Material Specifications

Body	Brass
Outer/Center	Brass
Contacts Insulator	PTFE
Ferrule	Brass
Finish	3 Min Gold Microninch Over 50 Microninch Copper



**Connect With Winchester Engineers
Request A Quote**

Mechanical Dimensions

All Dimensions are in millimeters

