

BRADY PORTABLE PRINTER COMPARISON



	CONTRACTOR SERIES			WORKSPACE SERIES		
	M210	M211	M410	M210-LAB	M510	M511
Max Label Width Inches (mm)	0.75 (19.1)	0.75 (19.1)	1.0 (25.4)	0.75 (19.1)	1.5 (38.1)	1.5 (38.1)
Print Speed in./ sec (mm/sec)	0.4 (10.2)	0.6 (15.2)	1.33 (33.0)	0.4 (10.2)	1.5 (38.1)	1.33 (33.0)
Print quality (dpi)	203	203	300	203	300	300
Maximum labels per day	100	100	250	100	500	500
Applications	Wire and cable DataCom Electrical Lean / 5S General identification	Wire and cable DataCom Electrical Lean / 5S General identification	DataCom Electrical Wire and cable General identification	Laboratory General identification	Laboratory Component & Equipment Wire and cable DataCom Electrical Lean / 5S General Identification Safety and Facility Construction	Laboratory Component & Equipment Wire and cable DataCom Electrical Lean / 5S General Identification Safety and Facility Construction
Material types	12	12	12	12	26	26
Label parts	90+	90+	110+	90+	250+	250+
Compatible media	M21-	M21-	M4-, M4C-	M21-	M4- M4C-, M5-, M5C-	M4- M4C-, M5-, M5C-
Print options	ABC Keypad	Mobile device	PC Connect QWERTY Keypad	ABC Keypad	PC Connect QWERTY Keypad	Mobile device PC Connect
Cutter type	Manual Cutter	Auto Cutter, with label retention	Manual Cutter	Manual Cutter	Manual Cutter	Auto Cutter, with label retention
Durability	Resistant to 6 foot drops, Military-grade shock resistance (MIL-STD-810G)	Resistant to 6 foot drops, Military-grade shock resistance (MIL-STD-810G), Resistant to 250-lb crushes	Resistant to 4 foot drops	Resistant to 6 foot drops	Resistant to 4 foot drops	Resistant to 6 foot drops, Military-grade shock resistance (MIL-STD-810G), Blowing sand and dust, Resistant to 250-lb crushes
Kits available	M210-KIT	M211-KIT	M410-KIT M410-PWID M410-SFID	—	M510-KIT M510-PWID M510-SFID M510-LAB	M511-KIT M511-SFID
Built-in wizards	Wire marker, terminal block, patch panel, custom length, fixed length, flag label, breaker box, banner landscape, portrait landscape	Wire wrap, terminal block, patch panel, flag label, breaker box, blank, vial, tube, slide, sleeve	Patch panel, wire marker, flag label, terminal block, desistrip, 66 block, 110 block, BIX block	Vial, custom length, fixed length, banner landscape, portrait landscape	Patch panel, wire marker, flag label, terminal block, desistrip, 66 block, 110 block, BIX block, vial	Wire wrap, terminal block, patch panel, flag label, breaker box, blank, vial, tube, slide, sleeve
Connectivity Options	—	Bluetooth (Single Connection)	USB	—	USB	USB and Bluetooth (Up to 5 concurrent connections)
Software compatibility	—	Express Labels Mobile App	Brady Workstation	—	Brady Workstation	Express Labels Mobile App, Brady Workstation
Power options	6 AA batteries, Rechargeable Li-ION battery, AC adapter	Non-Removable Rechargeable Li-ION battery, AC adapter	Rechargeable NiMH battery, AC adapter	6 AA batteries, Rechargeable Li-ION battery, AC adapter	Rechargeable NiMH, Rechargeable Li-ION battery, AC adapter	Non-Removable Rechargeable Li-ION battery, AC adapter

FLEX SERIES		
M610	M611	M710
2.0 (50.8)	2.0 (50.8)	2.0 (50.8)
2.0 (50.8)	2.0 (50.8)	3.0 (76.2)
300	300	300
750	750	1000
Asset Tracking Circuit Board Labeling Data and Telecommunications Labeling Electrical Labeling General Identification Wire and Cable Labeling Facility Identification Safety Identification	Asset Tracking Circuit Board Labeling Component and Equipment Labeling Data and Telecommunications Labeling Electrical Labeling General Identification Laboratory Labeling Wire and Cable Labeling Facility Identification Safety Identification	Circuit Board Labeling Datacom and Telecommunications Labeling Electrical Labeling General Identification Inspection Repair Lean / 5S Pipe Marker Rating & Name Plates Safety Identification Wire and Cable Labeling Facility Identification
50+	50+	60+
900+	900+	1400+
M6-, M6C-, BM-, BMC-	M6-, M6C-, BM-, BMC-	M7-, M7C-, BM7-, BM7C-, BMC-, BM-, M6-, M6C-
PC Connect, QWERTY Keypad <small>*Bluetooth and mobile device capable models available</small>	Mobile device, PC Connect	PC Connect, QWERTY Keypad <small>*Bluetooth and mobile device capable models available</small>
Manual Cutter	Auto Cutter, with label retention	Auto Cutter
Resistant to 6 foot drops, Military-grade shock resistance (MIL-STD-810G)	Resistant to 4 foot drops, Military-grade shock resistance (MIL-STD-810G)	Resistant to 4 foot drops, Blowing sand and dust (MIL-STD-810G)
M610-KIT M610-B-KIT M610-B-SFID M610-B-PWID	M611-SFID M611-PWID M611-LAB	M710-KIT M710-WB-KIT M710-WB-SFID M710-WB-PWID
66 Block, Breaker Box, DesiStrip, Flags, General, Patch Panel, Terminal Block, Wire Wrap	Wire wrap, terminal block, patch panel, flag label, breaker box, blank, vial, tube, slide, sleeve	Pipe Marker, Wire Wrap, Arrow Tape, Breaker Box, DesiStrip, Face Plate, Flags, Patch Panel, Terminal Block, Vial, Safety, 66 Block
USB and Bluetooth (Single Connection)	USB, Wi-Fi and Bluetooth (Up to 5 concurrent connections)	USB, Wi-Fi and Bluetooth (Up to 5 concurrent connections)
Brady Workstation, Express Labels Mobile App	Brady Workstation, Express Labels Mobile App	Brady Workstation, Express Labels Mobile App
Rechargeable Li-ION Battery, AC adapter	Rechargeable Li-ION Battery, AC adapter	Rechargeable Li-ION Battery, AC adapter

PRINT LIKE A PRO

All Brady portable printers are made to get the job done



Built to work

Ready for any jobsite, our printers have been put to the test to ensure industrial-grade performance every single time.



High-performance label options

From field to facility to lab, you can rely on durable, purpose-built materials that perform.



Connectivity flexibility

Find connectivity options to create labels quickly and easily whether you're in the office or on the go.



Industry-leading coverage

We stand behind our products which is why all portable printers come with a 2-year warranty and unrivaled tech support.