


RoHS
Ready 



HVS High Variable System Modular System Overview

Engineering Notes

A large, empty grid of small squares, intended for writing engineering notes. The grid covers most of the page area below the 'Engineering Notes' header and above the footer.

Introduction

HTS Portrait

HTS a brand of TE Connectivity (TE) has knowledge in developing and manufacturing heavy duty connectors for more than 50 years.

Customers in industrial machinery, electrical power utilities and specially railway trust in the extremely high quality standards and the greatest product offer. The product portfolio includes standard products, latest innovations as well as customer specific solutions to fulfill the highest customer requirements.

With production lines in strategic countries and regions TE as a local content partner is setting benchmarks in the market and is also offering a great customer service with an individual support from experts.

HVS Modular System

The HVS Modular System (high variable system) offers a maximum of flexibility and reliability with a minimum of installation or maintenance effort.

This system enables a realization of application specific connectors and the combination variety of the different inserts leads to reduced costs and less mounting space. The HVS range comprises more than 25 different modules and the particular zinc frames which can then be mounted into all hoods and housings from TE. There is no tooling needed to put the modules in and out of the frame due to lever snap-in technology.


Up to 6 modules can be used in a size 8 frame whereby the customer can individually define the combination of modules.

Signal, high current and high voltage, high density, Fire Wire, RJ45, USB, coax, twisted pair, high speed and also pneumatic modules are only some of the available modules. Contact cavities can be loaded individually which leads to an additional cost reduction.





Technical Support

Customers appreciate the individual support from technical specialists.






Contact us by phone, email or live chat.
te.com/help




Overview Module Inserts

Type	HVS-HF8	HVS-HF6	HVS-GND	HVS-HV
				
max. Voltage V	1000	1000 (150 HN.D)		5000
max. Current A	250	150		16
No. of Contacts	1	2 (HF6)+ 8 (HN.D)	1	2
Male Insert	HVS-HF.08.1.Sti.C	HVS-HF.06.2+8.Sti.C	HVS-GND	HVS-HV.2.Sti.C
Part No.	0-1103248-1	0-1103242-1	0-1103229-1	0-1103156-1
Female Insert	HVS-HF.08.1.Bu.C	HVS-HF.06.2+8.Bu.C	HVS-GND	HVS-HV.2.Bu.C
Part No.	0-1103249-1	0-1103243-1	0-1103229-1	0-1103157-1
Main Kontakt	Crimp HF8	Crimp HF6	Crimp HF6	Crimp HVT
Diameter mm ²	6-70 (opt. Crimp Ferrule)	6-50 (opt. Crimp Ferrule)	6-35 (opt. Crimp Ferrule)	0,13-4
Male Insert	Crimp HF8	Crimp HF6	Crimp HF6	Pin Ag 0,13-0,4 mm ²
Part No.	0-1103037-1 (+ Crimp Ferrule)	0-1110948-2 (+ Crimp Ferrule)	0-1110948-2 (+ Crimp Ferrule)	6-1105300-1
Male Insert				Pin Ag 0,5 mm ²
Part No.				1-1105300-1
Male Insert				Pin Ag 0,75-1,0 mm ²
Part No.				2-1105300-1
Male Insert				Pin Ag 1,5 mm ²
Part No.				3-1105300-1
Male Insert				Pin Ag 2,5 mm ²
Part No.				4-1105300-1
Male Insert				Pin Ag 4,0 mm ²
Part No.				5-1105300-1
Female Insert				Socket Ag 0,13-0,4 mm ²
Part No.	0-1103038-1 (+ Crimp Ferrule)	0-1110949-2 (+ Crimp Ferrule)	0-1110949-2 (+ Crimp Ferrule)	6-1105301-1
Female Insert				Socket Ag 0,5 mm ²
Part No.				1-1105301-1
Female Insert				Socket Ag 0,75-1,0 mm ²
Part No.				2-11053011
Female Insert				Socket Ag 1,5 mm ²
Part No.				3-1105301-1
Female Insert				Socket Ag 2,5 mm ²
Part No.				4-1105301-1
Female Insert				Socket Ag 4,0 mm ²
Part No.				5-1105301-1
Hand Tool incl. Die Set	HSS-CSZ.2,5-70 mm ²	HSS-CSZ.2,5-70 mm ²	HSS-CSZ.2,5-70 mm ²	RSZ.HE-HN.D-HVT
Part No.	1-1105653-8 + X-1105653-8	1-1105653-8 + X-1105653-8	1-1105653-8 + X-1105653-8	1-1105851-8
Insertion Tool				EWZG-RSZ
Part No.				0-1102855-6
Extraction Tool				AWZG-RSZ
Part No.				0-1102855-3
Accessories	Crimp Ferrule HF8	Crimp Ferrule HF6	Crimp Ferrule HF6	
	Crimp Ferrule 6 mm ²	Crimp Ferrule 6 mm ²	Crimp Ferrule 6 mm ²	
	0-1110952-1	0-1108807-1	0-1108807-1	
	Crimp Ferrule 10 mm ²	Crimp Ferrule 10 mm ²	Crimp Ferrule 10 mm ²	
	0-1110952-2	0-1108807-2	0-1108807-2	
	Crimp Ferrule 16 mm ²	Crimp Ferrule 16 mm ²	Crimp Ferrule 16 mm ²	
	0-1110952-3	0-1108807-3	0-1108807-3	
	Crimp Ferrule 25 mm ²	Crimp Ferrule 25 mm ²	Crimp Ferrule 25 mm ²	
	0-1110952-5	0-1108807-4	0-1108807-4	
	Crimp Ferrule 35 mm ²	Crimp Ferrule 35 mm ²	Crimp Ferrule 35 mm ²	
	0-1110952-7	0-1108807-5	0-1108807-5	
	Crimp Ferrule 50 mm ²	Crimp Ferrule 50 mm ²	Crimp Ferrule 50 mm ²	
	0-1110952-9	0-1108807-6	0-1108807-6	
	Crimp Ferrule 70 mm ²			
	1-1110952-0			
		HN.D Contacts & Tooling see HVS-HN.D.12		

Overview Module Inserts

HVS-HSS.2	HVS-HSK.2	HVS-HSK.3	HVS-HE.5-SC	HVS-HE.6
				
500 63 2	1000 40 2	400/690 40 3	400 16 5	500 16 6
HVS-HSS.2.Sti.C 0-1103275-1	HVS-HSK.2.Sti.C 0-1103270-1	HVS-HSK.3.Sti.C 0-1103272-1	HVS-HE.5.Sti.SC 0-1103133-1	HVS-HE.6.Sti.C 0-1103244-1
HVS-HSS.2.Bu.C 0-1103274-1	HVS-HSK.2.Bu.C 0-1103271-1	HVS-HSK.3.Bu.C 0-1103273-1	HVS-HE.5.Bu.SC 0-1103134-1	HVS-HE.6.Bu.C 0-1103245-1
Crimp HSS 2,5-16	Crimp HSK 1,5-10	Crimp HSK 1,5-10	Spring Clamp SC 0,14-2,5	Crimp HE/HA 0,5-4
Pin Ag 6,0 mm ² 3-1105150-1	Pin Ag 1,5 mm ² 1-1108757-1	Pin Ag 1,5 mm ² 1-1108757-1		Pin Ag Ag 0,5 mm ² 1-1105100-1
Pin Ag 10,0 mm ² 4-1105150-1	Pin Ag 2,5 mm ² 2-1108757-1	Pin Ag 2,5 mm ² 2-1108757-1		Pin Ag 0,75-1 mm ² 2-1105100-1
Pin Ag 16,0 mm ² 5-1105150-1	Pin Ag 4 mm ² 3-1108757-1	Pin Ag 4 mm ² 3-1108757-1		Pin Ag 1,5 mm ² 3-1105100-1
	Pin Ag 6 mm ² 4-1108757-1	Pin Ag 6 mm ² 4-1108757-1		Pin Ag 2,5 mm ² 4-1105100-1
	Pin Ag 10 mm ² 5-1108757-1	Pin Ag 10 mm ² 5-1108757-1		Pin Ag 4 mm ² 5-1105100-1
Socket Ag 6,0 mm ² 3-1105151-1	Socket Ag 1,5 mm ² 1-1108756-1	Socket Ag 1,5 mm ² 1-1108756-1		Socket Ag 0,5 mm ² 1-1105101-1
Socket Ag 10,0 mm ² 4-1105151-1	Socket Ag 2,5 mm ² 2-1108756-1	Socket Ag 2,5 mm ² 2-1108756-1		Socket Ag 0,75-1 mm ² 2-1105101-1
Socket Ag 16,0 mm ² 5-1105151-1	Socket Ag 4 mm ² 3-1108756-1	Socket Ag 4 mm ² 3-1108756-1		Socket Ag 1,5 mm ² 3-1105101-1
	Socket Ag 6 mm ² 4-1108756-1	Socket Ag 6 mm ² 4-1108756-1		Socket Ag 2,5 mm ² 4-1105101-1
	Socket Ag 10 mm ² 5-1108756-1	Socket Ag 10 mm ² 5-1108756-1		Socket Ag 4 mm ² 5-1105101-1
RSZ.BAS (+ Die Set) 1-1105850-8	RSZ.BAS (+ Die Set) 1-1105850-8	RSZ.BAS (+ Die Set) 1-1105850-8		RSZ.HE-HN.D-HVT 1-1105851-8
	EWZG-RSZ 0-1102855-6	EWZG-RSZ 0-1102855-6		EWZG-RSZ 0-1102855-6
AWZG-HSS-RSZ 0-1102855-5	AWZG-HSK-RSZ 0-1102855-8	AWZG-HSK-RSZ 0-1102855-8		AWZG-HE-Q5-RSZ 0-1102855-7
Die Sets	Die Sets	Die Sets		
Die 6+25 mm ² 1-1105652-8	Die 0,75-2,5 mm ² 0-1102789-1	Die 0,75-2,5 mm ² 0-1102789-1		
Die 10+16 mm ² 2-1105652-8	Die 4-10 mm ² 0-1102790-1	Die 4-10 mm ² 0-1102790-1		




Overview Module Inserts

HVS-HE.6P	HVS-HE.8	HVS-HE.20	HVS-HN.D.12	HVS-HN.D.17
				
830 16 6	400 16 8	500 16 20	250 10 12	250 10 17
HVS-HE.6P.Sti.C 0-1103150-1	HVS-HE.8.Sti.C 0-1103140-1	HVS-HE.20.Sti.C 0-1103144-1	HVS-HN.D.12.Sti.C 0-1103277-1	HVS-HN.D.17.Sti.C 0-1103278-1
HVS-HE.6P.Bu.C 0-1103151-1	HVS-HE.8.Bu.C 0-1103141-1	HVS-HE.20.Bu.C 0-1103145-1	HVS-HN.D.12.Bu.C 0-1103276-1	HVS-HN.D.17.Bu.C 0-1103279-1
Crimp HE/HA 0,5-4	Crimp HE/HA 0,5-4	Crimp HE/HA 0,5-4	Crimp HN.D 0,14-2,5	Crimp HN.D 0,14-2,5
Pin Ag Ag 0,5 mm ² 1-1105100-1	Pin Ag Ag 0,5 mm ² 1-1105100-1	Pin Ag Ag 0,5 mm ² 1-1105100-1	Pin Ag 0,14-0,37 mm ² 1-1105050-1	Pin Ag 0,14-0,37 mm ² 1-1105050-1
Pin Ag 0,75-1 mm ² 2-1105100-1	Pin Ag 0,75-1 mm ² 2-1105100-1	Pin Ag 0,75-1 mm ² 2-1105100-1	Pin Ag 0,5 mm ² 2-1105050-1	Pin Ag 0,5 mm ² 2-1105050-1
Pin Ag 1,5 mm ² 3-1105100-1	Pin Ag 1,5 mm ² 3-1105100-1	Pin Ag 1,5 mm ² 3-1105100-1	Pin Ag 0,75-1 mm ² 3-1105050-1	Pin Ag 0,75-1 mm ² 3-1105050-1
Pin Ag 2,5 mm ² 4-1105100-1	Pin Ag 2,5 mm ² 4-1105100-1	Pin Ag 2,5 mm ² 4-1105100-1	Pin Ag 1,5 mm ² 4-1105050-1	Pin Ag 1,5 mm ² 4-1105050-1
Pin Ag 4 mm ² 5-1105100-1	Pin Ag 4 mm ² 5-1105100-1	Pin Ag 4 mm ² 5-1105100-1	Pin Ag 2,5 mm ² 5-1105050-1	Pin Ag 2,5 mm ² 5-1105050-1
Socket Ag 0,5 mm ² 1-1105101-1	Socket Ag 0,5 mm ² 1-1105101-1	Socket Ag 0,5 mm ² 1-1105101-1	Socket Ag 0,14-0,37 mm ² 1-1105051-1	Socket Ag 0,14-0,37 mm ² 1-1105051-1
Socket Ag 0,75-1 mm ² 2-1105101-1	Socket Ag 0,75-1 mm ² 2-1105101-1	Socket Ag 0,75-1 mm ² 2-1105101-1	Socket Ag 0,5 mm ² 2-1105051-1	Socket Ag 0,5 mm ² 2-1105051-1
Socket Ag 1,5 mm ² 3-1105101-1	Socket Ag 1,5 mm ² 3-1105101-1	Socket Ag 1,5 mm ² 3-1105101-1	Socket Ag 0,75-1 mm ² 3-1105051-1	Socket Ag 0,75-1 mm ² 3-1105051-1
Socket Ag 2,5 mm ² 4-1105101-1	Socket Ag 2,5 mm ² 4-1105101-1	Socket Ag 2,5 mm ² 4-1105101-1	Socket Ag 1,5 mm ² 4-1105051-1	Socket Ag 1,5 mm ² 4-1105051-1
Socket Ag 4 mm ² 5-1105101-1	Socket Ag 4 mm ² 5-1105101-1	Socket Ag 4 mm ² 5-1105101-1	Socket Ag 2,5 mm ² 5-1105051-1	Socket Ag 2,5 mm ² 5-1105051-1
RSZ.HE-HN.D-HVT 1-1105851-8	RSZ.HE-HN.D-HVT 1-1105851-8	RSZ.HE-HN.D-HVT 1-1105851-8	RSZ.HE-HN.D-HVT 1-1105851-8	RSZ.HE-HN.D-HVT 1-1105851-8
EWZG-RSZ 0-1102855-6	EWZG-RSZ 0-1102855-6	EWZG-RSZ 0-1102855-6	EWZG-RSZ 0-1102855-6	EWZG-RSZ 0-1102855-6
AWZG-HE-Q5-RSZ 0-1102855-7	AWZG-HE-Q5-RSZ 0-1102855-7	AWZG-HE-Q5-RSZ 0-1102855-7	AWZG-HN.D-RSZ 0-1102855-2	AWZG-HN.D-RSZ 0-1102855-2






Overview Module Inserts

HVS-S20DF.25	HVS-SMD.9	HVS-TX.2		Type
				
50 5 25	50 5 9	50 10 2x4 + Screen	50 5 2x8 + Screen	max. Voltage V max. Current A No. of Contacts
HVS-S20DF.25.Sti.C 0-1103260-1	HVS-SMD.9.Sti.C 0-1103158-1	HVS-TX.2.Sti 0-1103267-1	HVS-TX.2.Sti 0-1103267-1	Male Insert Part No.
HVS-S20DF.25.Bu.C 0-1103261-1	HVS-SMD.9.Bu.C 0-1103159-1	HVS-TX.2.Bu 0-1103269-1	HVS-TX.2.Bu 0-1103269-1	Female Insert Part No.
Crimp S20DF 0,08-0,6	Crimp S20DF 0,08-0,6	Crimp HN.D 0,14-2,5	Crimp S20DF 0,08-0,6	Main Contact Diameter mm ²
Pin Sn 0,08-0,2 mm ² 66507-9	Pin Sn 0,08-0,2 mm ² 66507-9	Pin Ag 0,14-0,37 mm ² 1-1105050-1	Pin Sn 0,08-0,2 mm ² 66507-9	Male Insert Part No.
Pin Sn 0,2-0,6 mm ² 66506-9	Pin Sn 0,2-0,6 mm ² 66506-9	Pin Ag 0,5 mm ² 2-1105050-1	Pin Sn 0,2-0,6 mm ² 66506-9	Male Insert Part No.
		Pin Ag 0,75-1 mm ² 3-1105050-1		Male Insert Part No.
		Pin Ag 1,5 mm ² 4-1105050-1		Male Insert Part No.
		Pin Ag 2,5 mm ² 5-1105050-1		Male Insert Part No.
Socket Sn 0,08-0,2 mm ² 66505-9	Socket Sn 0,08-0,2 mm ² 66505-9	Socket Ag 0,14-0,37 mm ² 1-1105051-1	Socket Sn 0,08-0,2 mm ² 66505-9	Female Insert Part No.
Socket Sn 0,2-0,6 mm ² 66504-9	Socket Sn 0,2-0,6 mm ² 66504-9	Socket Ag 0,5 mm ² 2-1105051-1	Socket Sn 0,2-0,6 mm ² 66504-9	Female Insert Part No.
		Socket Ag 0,75-1 mm ² 3-1105051-1		Female Insert Part No.
		Socket Ag 1,5 mm ² 4-1105051-1		Female Insert Part No.
		Socket Ag 2,5 mm ² 5-1105051-1		Female Insert Part No.
				Female Insert Part No.
Certi-Crimp 169424-1	Certi-Crimp 169424-1	RSZ.HE-HN.D-HVT 1-1105851-8	Certi-Crimp 169424-1	Hand Tool incl. Die Set Part No.
S20DF 726363-1	S20DF 726363-1	EWZG-RSZ 0-1102855-6	S20DF 726363-1	Insertion Tool Part No.
S20DF 91285-1	S20DF 91285-1	AWZG-HN.D-RSZ 0-1102855-2	S20DF 91285-1	Extraction Tool Part No.
		Inserts HN.D.4	Inserts S20DF.8	Accessories
		HVS-TX.HN.D.4.Sti.C 0-1103283-1	HVS-TX.S20DF.8.Sti.C 0-1103291-1	
		HVS-TX.HN.D.4.Bu.C 0-1103286-1	HVS-TX.S20DF.8.Bu.C 0-1103297-1	

Overview Module Inserts

Type	HVS-MVB.4		HVS-MM.17	HVS-Air.2
				
max. Voltage V	50	50	250	
max. Current A	10	5	10	
No. of Contacts	4 + Screen	8 + Screen	17	2
Male Insert	HVS-MVB.4.Sti.C	HVS-MVB.S20DF.8Sti.C	HVS-MM.17.Sti.C	HVS-Air.2.Sti
Part No.	0-1103251-1	0-1103258-1	0-1103280-1	0-1103246-1
Female Insert	HVS-MVB.4.Bu.C	HVS-MVB.S20DF.8.Bu.C	HVS-MM.17.Bu.C	HVS-Air.2.Bu
Part No.	0-1103253-1	0-1103259-1	0-1103281-1	0-1103247-1
Main Kontakt	Crimp HN.D	Crimp S20DF	Crimp HD.M	Pneumatic
Diameter mm ²	0,14-2,5	0,08-0,6	0,3-2,5	D = 4 mm
Male Insert	Pin Ag 0,14-0,37 mm ²	Pin Sn 0,08-0,2 mm ²	Pin Sn 0,3-0,56 mm ²	Pin 4 mm
Part No.	1-1105050-1	66507-9	1-1105000-3	0-1105354-1
Male Insert	Pin Ag 0,5 mm ²	Pin Sn 0,2-0,6 mm ²	Pin Sn 0,5-1,5 mm ²	
Part No.	2-1105050-1	66506-9	2-1105000-3	
Male Insert	Pin Ag 0,75-1 mm ²		Pin Sn 1,5-2,5 mm ²	
Part No.	3-1105050-1		4-1105000-3	
Male Insert	Pin Ag 1,5 mm ²			
Part No.	4-1105050-1			
Male Insert	Pin Ag 2,5 mm ²			
Part No.	5-1105050-1			
Male Insert				
Part No.				
Female Insert	Socket Ag 0,14-0,37 mm ²	Socket Sn 0,08-0,2 mm ²	Socket Sn 0,3-0,56 mm ²	Socket 4 mm with Valve
Part No.	1-1105051-1	66505-9	1-1105001-3	0-1105355-1
Female Insert	Socket Ag 0,5 mm ²	Socket Sn 0,2-0,6 mm ²	Socket Sn 0,5-1,5 mm ²	Socket 4 mm without Valve
Part No.	2-1105051-1	66504-9	2-1105001-3	0-1105355-2
Female Insert	Socket Ag 0,75-1 mm ²		Socket Sn 1,5-2,5 mm ²	
Part No.	3-1105051-1		4-1105001-3	
Female Insert	Socket Ag 1,5 mm ²			
Part No.	4-1105051-1			
Female Insert	Socket Ag 2,5 mm ²			
Part No.	5-1105051-1			
Female Insert				
Part No.				
Hand Tool incl. Die Set	RSZ.HE-HN.D-HVT	Certi-Crimp	RSZ.BAS (+ Die Set)	
Part No.	1-1105851-8	169424-1	1-1105850-8	
Insertion Tool	EWZG-RSZ	S20DF	EWZG-RSZ	
Part No.	0-1102855-6	726363-1	0-1102855-6	
Extraction Tool	AWZG-HN.D-RSZ	S20DF	AWZG-HD.M-RSZ	AWZG-AIR
Part No.	0-1102855-2	91285-1	0-1102855-1	0-1102985-1
Accessories			Die Sets	
			Die 0,2-2,5 mm ²	
			0-0539668-2	
			Alternative Contacts	
			Fibre	
			Coaxial	
			Crimp	
			High Current	
			Alternative Contacts and Tooling please contact PIC	

Overview Module Inserts

HVS-RJ45	HVS-USB	HVS-FW	HVS-Quadrx	HVS-BLD
				
Cat 5 Cat 5 8	USB USB 4	IEEE P1394 IEEE P1394 6	100/1000 Base T <100 MHz 100/1000 Base T <100 MHz 4 + Screen	
HVS-RJ45.Sti 0-1103189-1	HVS-USB.Sti 0-1103180-1	HVS-FW.Sti 0-1103184-1	HVS-Quadrx.2.Sti 0-1103382-1	HVS-BLD 0-1103266-1
HVS-RJ45.Bu 0-1103192-1	HVS-USB.Bu 0-1103179-1	HVS-FW.Bu 0-1103183-1	HVS-Quadrx.2.Bu 0-1103381-1	
To be used with screened RJ45 Patch Cable	To be used with screened USB Patch Cable	To be used with screened FireWire Patch Cable	To be used with Quadrx Connectors	
RJ45 Patch Cable	USB Patch Cable	FireWire Patch Cable	Quadrx Connectors Plug incl. Contacts 0-1445692-1 Socket incl. Contacts 0-1445693-1	
			Contact Crimp Tool 601966-1 + 8-1579013-9	
			Ferrule Crimp Tool 608650-1 + 0-1579016-7	
Patch Cable please contact PIC	Patch Cable please contact PIC	Patch Cable please contact PIC	Patch Cable please contact PIC	

Accessories

HVS Frames


The HVS zinc die-cast frames for the HVS modular inserts distinguish with a variety of innovative solutions. TE developed one piece frames to prevent the loss of modules during the installation and maintenance process and offers a more reliable and user-friendly solution. The moulded pin and socket contact for ground (first make last break) ensure additional stability and improved performance. Up to 6 single modules fit into a size 8 frame whereby guidances in the frame and the modules prevent twist

locking. The frames also capture coding set for up to 36 different coding positions and prohibit mixing up of damages due to interchanging of adjoining connectors. A tool-less insertion and extraction of modular inserts simplifies the handling and reduces tooling costs as well as installation time. Customer can individually configurate the frames which fit into all particular heavy duty connector hoods and housings from TE (see table).

Overview Frames

Housing	Size		No of Single Modules*	Part No.	
		Frame			
3		3	2	Top	0-1103250-7
				Bottom	0-1103250-8
4		4	3	Top	0-1103250-5
				Bottom	0-1103250-6
6		6	4	Top	0-1103250-3
				Bottom	0-1103250-4
8		8	6	Top	0-1103250-1
				Bottom	0-1103250-2
10		2x6	8 (2x4)	Top	0-1103250-3
				Bottom	0-1103250-4
12		2x8	12 (2x6)	Top	0-1103250-1
				Bottom	0-1103250-2

* 1 double module = 2 single modules



Overview Cable Glands IP68

Size Metric Thread	Plastic		Metal		EMI	
	Cable Ø (mm)	Part No.	Cable Ø (mm)	Part No.	Cable Ø (mm)	Part No.
M16	4-8	1-1102771-6	5-10	1-1102770-6	5-9	1-1102772-6
M20	6-12	2-1102771-0	6-12	2-1102770-0	8-13	2-1102772-0
M25	10-14	2-1102771-5	13-18	2-1102770-5	11-16	2-1102772-5
M32	13-18	3-1102771-2	18-25	3-1102770-2	15-21	3-1102772-2
M40	18-25	4-1102771-0	22-32	4-1102770-0	19-27	4-1102772-0
M50	22-32	5-1102771-0	32-38	5-1102770-0	26-35	5-1102772-0

PG cable glands on request.

Cable Glands IP68

- Plastic, metal and EMI versions available
- EMI version to prevent electro magnetic interferences



Coding Set

- 36-position coding set
- Part No. 530341-1



Screen Termination

















- Size 3: 0-1103256-1
- Size 4: 0-1103256-2
- Size 6: 0-1103256-3
- Size 8: 0-1103256-4







For questions or further information on additional accessories please contact our specialists in TE's Product Information Centers: te.com/help

Accessories

Overview Crimp Contacts

Contacts	Pin Contact	Socket Contact	Contacts	Pin Contact	Socket Contact
HF8/HF6	 Screwed Contacts	 Screwed Contacts	HSK	 Screwed Contacts	 Screwed Contacts
HD.M	 Stamped Contacts	 Stamped Contacts	HE/HA	 Screwed Contacts	 Screwed Contacts
HVT	 Screwed Contacts	 Screwed Contacts	HN.D	 Screwed Contacts	 Screwed Contacts
HSS	 Screwed Contacts	 Screwed Contacts	S20DF	 Stamped Contacts	 Stamped Contacts

Hand Crimping Tools

Contacts	Hand Crimping Tool	Part No.	Locator/Die	Part No.	Insertion Tool	Part No.	Extraction Tool	Best.-Nr.
								
HF8	HSS-CSZ.2,5-70 mm ²	1-1105653-8		X-1105653-8	-	-	-	-
HF6	HSS-CSZ.2,5-70 mm ²	1-1105653-8		X-1105653-8	-	-	-	-
HVT	RSZ.HE-HN.D-HVT	1-1105851-8	included		EWZG-RSZ	0-1102855-6*	AWZG-RSZ	0-1102855-3*
HSS	RSZ.BAS	1-1105850-8*	Die 6+25 mm ²	1-1105652-8*			AWZG-HSS-RSZ	0-1102855-5
			Die 10+16 mm ²	2-1105652-8				
HSK	RSZ.BAS	1-1105850-8*	Die 0,75-2,5 mm ²	0-1102789-1	EWZG-RSZ	0-1102855-6*	AWZG-HSK-RSZ	0-1102855-8
			Die 4-10 mm ²	0-1102790-1				
HE/HA	RSZ.HE-HN.D-HVT	1-1105851-8	included		EWZG-RSZ	0-1102855-6*	AWZG-RSZ	0-1102855-7
HN.D	RSZ.HE-HN.D-HVT	1-1105851-8	included		EWZG-RSZ	0-1102855-6*	AWZG-HN.D-RSZ	0-1102855-2
S20DF	Certi-Crimp	169424-1	included		S20DF	726363-1	S20DF	91285-1
HD.M	RSZ.BAS	1-1105850-8	Die 0,2-2,5 mm ²	0-0539668-2	EWZG-RSZ	0-1102855-6*	AWZG-HD.M-RSZ	0-1102855-1
Quadrax	Quad. Contacts	601966-1	Quad. Contacts	8-1579013-9	-	-	Quad. Contacts	1738894-1

see picture

Semi Automatic Crimping Machine

- SAFETY CRIMP. PRESS SSC-2FP
Part No. 0-1481004-7
- Adapter for all RSZ Die Sets (see also Hand Crimping Tool)
Part No. 1579000-7



For questions or further information on additional accessories please contact our specialists in TE's Product Information Centers: te.com/help

FOR MORE INFORMATION

te.com/industrial

TE Technical Support Center

Internet: te.com/help
USA: +1 (800) 522-6752
Canada: +1 (905) 475-6222
Mexico: +52 (0) 55-1106-0800
Latin/S. America: +54 (0) 11-4733-2200
Germany: +49 (0) 6251-133-1999
UK: +44 (0) 800-267666
France: +33 (0) 1-3420-8686
Netherlands: +31 (0) 73-6246-999
China: +86 (0) 400-820-6015

Part numbers in this brochure are RoHS Compliant*, unless marked otherwise.

*as defined www.te.com/leadfree

te.com

© 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights Reserved.

1308159-2 CIS WR 07/2011

HTS, TE Connectivity and the TE connectivity (logo) are trademarks.

Other logos, product and Company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this catalog, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

