

NOTES:


1. MATERIALS AND FINISHES:
 BODIES, SLEEVE & CAP - BRASS, NICKEL PLATING
 BODY REAR & CLAMP NUT - BRASS, SILVER PLATING
 CONTACTS & TUBE - BRASS, GOLD PLATING
 CONTACTS - BeCu, GOLD PLATING
 RETAINING RING - BeCu, NATURAL
 INSULATORS - PTFE, NATURAL
 GASKET - SILICONE RUBBER, RED
 FERRULE - COPPER, NICKEL PLATING
 HEAT SHRINK TUBE - WHITE

2. MECHANICAL:
 A. TEMPERATURE RANGE: -65°C TO +165°C


3. PACKAGING:
 A. QUANTITY: SINGLE PACK
 B. MARKING: PACKAGING TO BE MARKED
 "AMPHENOL RF, 31-34179-1 AND DATE CODE"

4 SHOWS CABLE ENTRY DIMENSIONS.

REVISIONS				
REV	DESCRIPTION	DATE	ECN	APPR
--	RELEASE TO MFG.	--	--	--
V	REDRAWN IN CREO AND COD SHEET ADDED	09-SEP-20	15318	CL



SCALE 1.000



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

NOTICE: These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE METRIC (INCHES) AND TOLERANCES ARE: $<0.5\text{mm} = \pm 0.05\text{mm}$ [$<0.020 = \pm 0.002$] $>0.5 - 6\text{mm} = \pm 0.1\text{mm}$ [$>0.020 - 0.236 = \pm 0.004$] $>6.00 - 30\text{mm} = \pm 0.2\text{mm}$ [$>0.236 - 1.181 = \pm 0.008$] $>30.00 - 120\text{mm} = \pm 0.3\text{mm}$ [$>1.181 - 4.725 = \pm 0.012$] ANGLES = $\pm 1^\circ$		MATERIAL SEE NOTES		TITLE TNC RA TRIAX PLUG FOR TWINAX CABLE CLAMP TYPE		Amphenol RF	
THIRD ANGLE PROJ. REFERENCE EAR#		ENGINEER O.BARTHELMES		DATE 14-MAY-20		SHEET NO. 2 OF 2		SCALE: 3.0:1.0	
						SIZE B		DRAWING NO. 31-34179-1 ITEM NO. 31-34179-1 PART NO. 31-34179-1	
								REV V	