

## AUDIO/VIDEO CABLE




Fig. 1




Fig. 2




Fig. 3




Fig. 4





Fig. 5

### Economy Audio/Video Cable

Retail Part No.	Bulk Part No.	Figure Number	Description	Cable Length
30-1706		1	Un-Shielded Single RCA Plug to RCA Plug; 2 Conductor 24 AWG	6m ('20')
30-1708		1	Un-Shielded Single RCA Plug to RCA Plug; 2 Conductor 24 AWG	12m ('40')
30-1705		1	Un-Shielded 18 AWG Single RCA Plug to RCA Plug; 2 Conductor	6m ('20')
30-1707		1	Un-Shielded 18 AWG Single RCA Plug to RCA Plug; 2 Conductor	12m ('40')
30-1856		2	Shielded Single Right Angle RCA Plug to Single Right Angle RCA Plug	2m ('6')
30-400		3	Shielded Single RCA Plug to RCA Plug; 2 Conductor	.5m ('1.5')
30-402	30-402-BU	3	Shielded Single RCA Plug to RCA Plug; 2 Conductor	1m ('3')
30-404	30-404-BU	3	Shielded Single RCA Plug to RCA Plug; 2 Conductor 6'	2m ('6')
30-406		3	Shielded Single RCA Plug to RCA Plug; 2 Conductor	3.75m ('12')
32-3148		3	RG-59 Phono (RCA-type) Plug to Phono (RCA-type) Plug	1m ('3')
32-3149		3	RG-59 Phono (RCA-type) Plug to Phono (RCA-type) Plug	2m ('6')
32-3150		3	RG-59 Phono (RCA-type) Plug to Phono (RCA-type) Plug	3m ('12')
30-426		4	Shielded Single RCA Plug to Single RCA Jack	1m ('3')
30-428		4	Shielded Single RCA Plug to Single RCA Jack	2m ('6')
30-430		4	Shielded Single RCA Plug to Single RCA Jack	3.75m ('12')
30-407	30-407-BU	5	Shielded Dual RCA Plugs to Dual RCA Plugs	1m ('3')
30-407-60		5	Shielded Dual RCA Plugs to Dual RCA Plugs-60 Pieces	1m ('3')
30-407-3		5	Shielded Dual RCA Plugs to Dual RCA Plugs-Gold	1m ('3')
30-408		5	Shielded Dual RCA Plugs to Dual RCA Plugs	2m ('6')
30-408-3		5	Shielded Dual RCA Plugs to Dual RCA Plugs-Gold	2m ('6')
30-408-50	30-408-BU	5	Shielded Dual RCA Plugs to Dual RCA Plugs-50 Pieces	2m ('6')
30-409	30-409-BU	5	Shielded Dual RCA Plugs to Dual RCA Plugs	3.75m ('12')
30-419		5	Shielded Dual RCA Plugs to Dual RCA Plugs-Stereo	5m ('16')
30-513		5	Shielded Dual RCA	7.6m ('25')

# AUDIO/VIDEO



## AUDIO/VIDEO CABLE (Cont.)




Fig. 1




Fig. 2




Fig. 3




Fig. 4



Fig. 5

### Audio/Video Cable

Retail Part No.	Bulk Part No.	Figure Number	Description	Cable Length
30-1827		1	Shielded Pistol Type Dual Plugs with RCA Jack Adapter to Dual RCA Plugs	2m ('6')
30-1828		1	Shielded Pistol Type Dual Plugs with RCA Jack Adapter to Dual RCA Plugs	3.75m ('12')
30-413		2	Shielded Car Stereo-Dual RCA to Dual RCA with Grounding Wire at Both Ends	5m ('16')
30-410		3	Dual Shielded RCA Plugs to Dual RCA Jacks	1m ('3')
30-411		3	Dual Shielded RCA Plugs to Dual RCA Jacks	2m ('6')
30-1537		4	Interconnect Cable Triple RCA Plug RWY-Gold	2m ('6')
30-1537-25		4	Interconnect Cable Triple RCA Plug RWY-Gold	2m ('6')
SD-1538		4	Dubbing Cable Triple RCA Plug RWY-Gold-Stereo	3.75m ('12')
32-3236		5	RG-59 Dual Phono (RCA-Type) Plug to Dual Phono (RCA-Type) Plug-Gold	2m ('6')

## AUDIO CABLE




Fig. 6




Fig. 7



Fig. 8



Fig. 9



Fig. 10

### Audio Cables

Retail Part No.	Bulk Part No.	Figure Number	Description	Length (Meters)	Ferrite Bead
65-1713-1M		6	Stereo Cable 3.5mm Phone Plug to 3.5mm Phone Plug	1	No
65-1719-1M		7	Stereo Cable 1/4" Phone Plug to 1/4" Phone Plug	1	No
65-1720-1M		8	Phone Plug 3.5mm Quad Plug to 3.5mm Quad Jack	1	No
65-1723-1M		9	Phone Plug 3.5mm Quad Plug to 3xRCA Plugs RWY	1	No
65-1726-1M		10	Phone Plug Rt. Angle 3.5mm Quad Plug to 3xRCA Plugs RWY	1	No

**AUDIO/VIDEO CABLE**

Fig. 1

~~Fig. 2~~

Fig. 3

**Audio Cables**

Retail Part No.	Bulk Part No.	Figure Number	Description	Length (Meters)	Ferrite Bead
65-1729-1M		1	Stereo Cable 3.5mm Phone Plug to 3.5mm Phone Plug-Metal Shell	1	No
<del>65-1729-3M</del>		<del>1</del>	<del>Stereo Cable 3.5mm Phone Plug to 3.5mm Phone Plug-Metal Shell</del>	<del>3.75</del>	<del>No</del>
<del>65-1730-3M</del>		<del>2</del>	<del>Stereo Cable 3.5mm Phone Plug to 3.5mm Phone Jack-Metal Shell</del>	<del>3.75</del>	<del>No</del>
65-1739-1M		3	Phone Plug 3.5mm Quad Plug to 3xRCA Plugs RWY-Metal Shell	1	No
65-1739-2M		3	Phone Plug 3.5mm Quad Plug to 3xRCA Plugs RWY-Metal Shell	2	No



Fig. 1



Fig. 2



Fig. 3




Fig. 4



Fig. 5

### Phono Pin Plug & Jack Combinations

Retail Part No.	Bulk Part No.	Figure Number	Description
30-510	30-510-BU	1	Phono Pin Plug to 2 Phono Pin Jacks
30-510-3		1	Phono Pin Plug to 2 Phono Pin Jacks-Gold
30-512	30-512-BU	2	Phono Pin Jack to 2 Phono Pin Plugs
30-512-3		2	Phono Pin Jack to 2 Phono Pin Plugs
30-514		3	Phono Pin Plug to 2 Phono Pin Plugs

### Standard Phone Plug & Jack Combinations

Retail Part No.	Bulk Part No.	Figure Number	Description
30-522		4	Standard Mono Phone Plug to 2 Standard Mono Phone Jacks
30-524		4	Standard Stereo Phone Plug to 2 Standard Mono Phone Jacks
30-1560		5	Standard Stereo Phone Plug to 2 Standard Stereo Phone Jacks

## AUDIO "Y" ADAPTERS (Cont.)



Fig. 1




Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7



Fig. 8

### Miniature Plug & Jack Combinations

Retail Part No.	Bulk Part No.	Figure Number	Description
30-1558		1	Miniature Phone Plug to 2 Miniature Phone Jacks
30-1559		2	Miniature Stereo Phone Plug to 2 Miniature Stereo Phone Jacks
30-1565		3	Miniature Stereo Phone Plug to 2 RCA Jacks (Basic)

### Metal "Y" Adapters

Retail Part No.	Bulk Part No.	Figure Number	Description
30-500		4	Standard Mono Phone Plug to 2 Mono Phono Pin Jacks
30-504		5	Mono Phono Pin Plug to 2 Mono Phono Pin Jacks

### Auto Antenna "Y" Connector

Retail Part No.	Bulk Part No.	Figure Number	Description
30-3081		6	Allows Hook-up of an Add. AM, FM, AM/FM Radio CB to Car Radio Antenna

### S-VHS "Y" Adapters

Retail Part No.	Bulk Part No.	Figure Number	Description
65-4401		7	1 S-VHS Plug to 2 S-VHS Jacks
65-4402		8	2 S-VHS Plugs to 1 S-VHS Jack



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7



Fig. 8



Fig. 9




Fig. 10



Fig. 11



Fig. 12

### Adapters

Retail Part No.	Bulk Part No.	Figure Number	Description
30-495	30-495-BU	1	3.5mm Mini Phone Plug to RCA Jack-all metal (Better)
30-472		2	1/4" Phone Plug to RCA Jack (Basic)
30-472-1		3	1/4" Mono Phone Plug to Mono 3.5mm Mini Phone Jack (Mono-Mono).(Basic)
30-478		4	2.5mm Subminiature Phone Plug to 3.5mm Phone Jack (Mono-Mono).(Basic)
30-1587		5	Mono 3.5mm Mini Phone Plug to Stereo 3.5mm Mini Phone Jack (Mono-Stereo).(Basic)
30-496		6	3.5mm Mini Phone Plug to 1/4" Phone Jack (Mono-Mono).(Basic)
30-1554		7	3.5mm Mini Phone Plug to 1/4" Stereo Phone Jack (Mono-Stereo).(Better)
30-1576		8	3.5mm Stereo Mini Phone Plug to 1/4" Stereo Phone Jack (Stereo-Stereo).(Basic)
30-1574		9	1/4" Stereo Phone Plug to 3.5mm Stereo Mini Phone Jack (Stereo-Stereo).(Basic)
30-1575		10	1/4" Stereo Phone Plug to 3.5mm Stereo Mini Phone Jack-Gold (Stereo-Stereo).(Best)
30-1571		11	3.5mm Stereo Mini Phone Jack to 3.5mm Stereo Mini Phone Jack (Stereo-Stereo).(Better)
30-1570		12	1/4" Mono Phone Jack to 1/4" Mono Phone Jack (Mono-Mono).(Basic)

## PHONE PLUG CABLES




Fig. 1




Fig. 2



Fig. 3




Fig. 4




Fig. 5




Fig. 6




Fig. 7




Fig. 8



Fig. 9




Fig. 10




Fig. 11



Fig. 12




Fig. 13




Fig. 14



Fig. 15




Fig. 16




Fig. 17

### Phone Plug Cables

Retail Part No.	Bulk Part No.	Figure Number	Description	Cable Length
30-401		1	Shielded Single RCA Plug to 3.5mm Mini Phone Plug	1m (~3')
30-403		1	Shielded Single RCA Plug to 3.5mm Mini Phone Plug	2m (~6')
30-1812		2	Shielded Dual RCA Plug to 3.5mm Stereo Mini Plug	2m (~6')
30-444		3	Shielded Single RCA Plug to 1/4" Phone Plug	2m (~6')
30-1830		4	2 Conductor 2.5mm Subminiature Plug to 2.5mm Subminiature Jack	6m (~20')
30-415		5	2 Conductor 3.5mm Mini Phone Plug to Stripped end Cable	2m (~6')
30-1808		6	2 Conductor 3.5mm Mini Phone Plug to 3.5mm Phone Plug	1m (~3')
30-1809		6	2 Conductor 3.5mm Mini Phone Plug to 3.5mm Phone Plug	2m (~6')
30-1806		7	2 Conductor 3.5mm Mini Phone Plug to 3.5mm Phone Jack	2m (~6')
30-1807		7	2 Conductor 3.5mm Mini Phone Plug to 3.5mm Phone Jack	3.75m (~12')
30-431		8	2 Conductor 3.5mm Mini Phone Plug to 1/4" Phone Plug	2m (~6')
30-434		9	3 Conductor 3.5mm Mini Phone Plug to 1/4" Phone Plug	2m (~6')
30-443		10	2 Conductor 1/4" Phone Plug to 1/4" Phone Plug	2m (~6')
30-556		11	Coiled 3 Conductor 1/4" Phone Plug to Right Angle 1/4" Phone Plug	6m (~20')
30-1821		12	3 Conductor Stereo 3.5mm Mini Phone Plug to Stereo 3.5mm Mini Phone Plug	2m (~6')
30-1811		13	3 Conductor Stereo 3.5mm Mini Phone Plug to Stereo 3.5mm Mini Phone Jack	3m (~10')
30-1824		14	3 Conductor Stereo 1/4" Phone Plug to Stereo 1/4" Phone Jack	6m (~20')
30-1825		15	Coiled 3 Conductor Stereo 1/4" Phone Plug to Stereo 1/4" Phone Jack	7.6m (~25')
30-1697		16	Microphone Cable Low Noise	5m (~16')
30-1695		17	Microphone Cable	6m (~20')