

ICM Connector and Tool System— The Best Way to Ensure Signal Quality From the Start

Use only the best connectors and tools from ICM. Specializing in F-Conn Industries cable connectors and CablePro installation tools.



Patented 360° Compression...

- Our patented 360° compression rings on all our connectors provide **TRUE 360° compression**. Get a quality signal with a permanent connection, eliminating future trouble spots because of poor connection quality.
- The radial design and patented internal ring system **reduces ingress/egress at the connector**.
- All-brass compression connectors plated in nickel or gold **withstand 80 pounds of pull out force** so you know your connection is solid.
- ICM's patented **non-blind entry on our connectors allows installers to see when the wire is set in the pin before compression**. Installers see the wire entering the pin at the base of the connector, ensuring a solid, secure connection every time. No guesswork involved.

In a Complete System....

- ICM incorporates all F-Conn connectors and CablePro tools into a complete system for each step of the installation process, **reducing costly errors and training time**.

Highest Quality Products and Manufacturing...

- ICM uses the **highest quality materials and metals on the market utilizing our proprietary manufacturing process**. There's **no cracking or snapping of connectors during compression** to ensure a permanent 360° compression right from the start.

F-Conn Industries Connectors:

- F Connectors
- RCA Connectors
- BNC Connectors
- Right Angle Connectors
- Available in 59, 6, 15 mini coax, 1 mini coax, plenum RG6 and plenum RG59
- Speaker series includes screw on attachments spade, banana and pin

Featured CablePro Installation Tools:

- CPLCCT-SLM Compression Tool
- PSA59/6 Cable Prep Tool
- PSA59/6/RGB Cable Prep Tool



Gold Series

ICM Quality Connectors for Custom Installations

F-Conn connectors are available in F, BNC, RCA, Right Angle, Speaker and Plenum, in sizes 59, 6, 1 mini coax, 15 mini coax and RG11.

F-Conn connectors feature our patented 360-degree compression and non-blind entry for a solid connection and maximum signal quality.



Nickel Series

Speaker Compression Connector Series

Speaker Series includes standard straight connector and a right angle connector so installers will be prepared for any custom speaker configurations. Available screw-on tips include banana, pin and spade. Connectors fit 10,12,14 and 16 AWG wire.



RGSPU Speaker Series



CPLCCT-SLM Compression Tool

CablePro Linear Compliant Compression Tool

ICM's patented CablePro linear compliant compression tool is designed with the professional installer in mind. Solid steel tool for maximum strength and durability, with a crafted design for lightweight ease of use. Includes four interchangeable tips to compress various types of connectors including BNC, nickel or gold F, RCA and right angle. Reduces the number of tools that installers need for custom installations.



PSA59/6 Cable Prep Tool

Cable Stripper—PSA59/6

Our PSA59/6 cable stripper is designed to strip RG59 through RG6 Quad. Unique adjustable dial moves the cutting blades for precision preparation with added convenience. The PSA59/6 is also equipped with our patented cable stop for a perfect cable preparation. Our patented RG6 flaring bit easily finishes the prep work before the connector is put in place, reducing valuable prep time. For installer convenience, the PSA59/6 tool comes with an extra replaceable razor cartridge.



PSA59/6/RGB Cable Prep Tool

Cable Stripper—PS59/6/RGB

Our PS59/6/RGB is specially designed for stripping RG59, RG6, RGB (mini) cable sizes. Patented cable stop creates the perfect cable preparation every time. Prepping mini and drop cable has never been easier or more accurate! For installer convenience, the PS59/6/RGB tool comes with an extra replaceable razor cartridge.