

# HC-B 24-ADP-3D 7-GY - Adapter plate



1661448

<https://www.phoenixcontact.com/pc/products/1661448>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



HEAVYCON adapter plate with a reinforced wall, three openings for D7 panel mounting base; type B24 on 3xD7, for panel cutouts of type B24; gray

## Commercial Data

Item number	1661448
Packing unit	10 pc
Minimum order quantity	1 pc
Product Key	BF7AZD
Catalog Page	Page 664 (C-2-2019)
GTIN	4017918155124
Weight per Piece (including packing)	33.66 g
Weight per Piece (excluding packing)	33.1 g
Customs tariff number	39269097
Country of origin	DE

# HC-B 24-ADP-3D 7-GY - Adapter plate

1661448

<https://www.phoenixcontact.com/pc/products/1661448>

## Technical Data


### Notes

General	For wall cutouts of type B24
---------	------------------------------

### Product properties

Type	B24
Product type	Adapter plate
Seal present	yes

### Dimensions

Dimensional drawing	
Width	52 mm
Height	7 mm
Length	150 mm
Drill hole distance, horizontal	130 mm
Drill hole distance, vertical	32 mm
Hole diameter	4.5 mm

### Installation dimensions

Width of the assembly cutout	36 mm
Length of the assembly cutout	113 mm

### Material specifications

Color	gray
Material	PA
Flammability rating according to UL 94	HB
Seal material	PTS

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 100 °C


# HC-B 24-ADP-3D 7-GY - Adapter plate



1661448

<https://www.phoenixcontact.com/pc/products/1661448>

## Drawings



Dimensional drawing

# HC-B 24-ADP-3D 7-GY - Adapter plate



1661448

<https://www.phoenixcontact.com/pc/products/1661448>

## Classifications

### ECLASS

ECLASS-10.0.1	27440201
ECLASS-9.0	27440201
ECLASS-11.0	27440201
ECLASS-12.0	27440201
ECLASS-13.0	27440201

### ETIM

ETIM 8.0	EC002309
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HC-B 24-ADP-3D 7-GY - Adapter plate



1661448

<https://www.phoenixcontact.com/pc/products/1661448>

## Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstraße 8  
D-32825 Blomberg  
+49 (0) 5235-3 00  
[info@phoenixcontact.com](mailto:info@phoenixcontact.com)