

Inline connector - IB IL SCN-12-ICP



2727611

<https://www.phoenixcontact.com/de/produkte/2727611>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Connector, color coded, for digital 4, or 16-channel Inline input terminals

Commercial Data

Item number	2727611
Packing unit	10 pc
Minimum order quantity	10 pc
Sales Key	O1 - Automatisierungssys.
Product Key	DRI1Z1
Catalog Page	Page 122 (C-6-2019)
GTIN	4017918168209
Weight per Piece (including packing)	22,12 g
Weight per Piece (excluding packing)	21,75 g
Customs tariff number	85366990
Country of origin	DE

Inline connector - IB IL SCN-12-ICP



2727611

<https://www.phoenixcontact.com/de/produkte/2727611>

Technical Data

Product properties

Product type	Plug
--------------	------

Connection data

Conductor cross section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross section AWG	28 ... 16
Stripping length	8 mm

Dimensions

Width	12 mm
Height	136.2 mm
Depth	41 mm

Inline connector - IB IL SCN-12-ICP




2727611

<https://www.phoenixcontact.com/de/produkte/2727611>

Approvals

 cUL Recognized Approval ID: FILE E 140324				
	Nominal Voltage U_N	Nominal Current I_N	Cross Section AWG	Cross Section mm^2
	24 V	10 A	26 - 16	-

 UL Recognized Approval ID: FILE E 140324				
	Nominal Voltage U_N	Nominal Current I_N	Cross Section AWG	Cross Section mm^2
	24 V	10 A	26 - 16	-

 EAC Approval ID: RU*DE*08.B.00529/19	
--	--

cULus Recognized	
-------------------------	--

Inline connector - IB IL SCN-12-ICP



2727611

<https://www.phoenixcontact.com/de/produkte/2727611>

Classifications

ECLASS

ECLASS-9.0	27242692
ECLASS-10.0.1	27242692
ECLASS-11.0	27242692

ETIM

ETIM 8.0	EC002584
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

Inline connector - IB IL SCN-12-ICP



2727611

<https://www.phoenixcontact.com/de/produkte/2727611>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Inline connector - IB IL SCN-12-ICP

2727611

<https://www.phoenixcontact.com/de/produkte/2727611>



Accessories

Labeling field

Labeling field - IB IL FIELD 2 - 2727501

<https://www.phoenixcontact.com/de/produkte/2727501>

Labeling field, width: 12.2 mm



Labeling field

Labeling field - IB IL FIELD 8 - 2727515

<https://www.phoenixcontact.com/de/produkte/2727515>

Labeling field, width: 48.8 mm



Inline connector - IB IL SCN-12-ICP

2727611

<https://www.phoenixcontact.com/de/produkte/2727611>

Insert strip

Insert strip - ESL 62X10 - 0809492

<https://www.phoenixcontact.com/de/produkte/0809492>

Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems:
Laser printer, mounting type: insert, lettering field size: 62 x 10 mm, Number of
individual labels: 72



Insert strip

Insert strip - ESL 62X46 - 0809502

<https://www.phoenixcontact.com/de/produkte/0809502>

Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems:
Laser printer, mounting type: insert, lettering field size: 62 x 46 mm, Number of
individual labels: 15



Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstraße 8
D-32825 Blomberg
+49 52 35/3-1 20 00
info@phoenixcontact.de