



ProWick® Desoldering Braid (Pure Rosin)

Desoldering Braid
1801-1813, 1826, 1828

Introduction

To insure quality and reliable service, we start with only the finest oxygen-free and oil-free fine gauge wire. Our 100% copper wick is then coated with flux, which cleans connections thoroughly during desoldering to insure maximum solderability. This thin coating of flux also provides dependable, long-lasting protection from oxidation. Techspray® vacuum seals its Pro Wick® in durable clear plastic to protect it from moisture and to prolong shelf life of the product. This special packaging ensures the highest possible quality from the factory to the production floor.

Features / Benefits

- Pure Rosin Type R Flux
- Advanced Braid Design
- Vacuum Packed
- Anti-Static Bobbin (1808-1813, 1826, 1828) are within 10^5 to 10^{11} ohms resistivity

Chemical Components

Abietic acid and homomorphous mixtures (Rosin).....	(8050-09-7)	<5%
---	-------------	-----

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Packaging and Availability

ProWick® Desoldering Braid is available in the following sizes:

1801-1805	5F, 10F, 25F, 50F, 100F, 500F
1806	5F, 25F, 100F, 500F
1808-1811	5F, 10F, 25F, 50F, 100F
1812	5F, 10F, 25F
1813	5F, 25F
1826	5F, 10F
1828	5F

Resources

Techspray® products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America
Tech Spray L.P.
P.O. Box 949
Amarillo, TX 79105
800-858-4043
email: tsales@techspray.com

Europe
Techspray International
UNIT 4, 44/46 Bunyan Road, Kempston
Bedford MK42 8HL United Kingdom
+44 (0) 1234 855443
email: tseurope@techspray.com

Countries Outside US
Call to locate a distributor
in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Tech Spray, L.P.
P.O. Box 949
Amarillo, TX 79105
www.techspray.com

[English MSDS](#)
[French MSDS](#)
[German MSDS](#)
[Italian MSDS](#)
[Spanish MSDS](#)

