

You can view this page in:

■ [EN](#) [DE](#) [SV](#) [FR](#) [C6](#) [DA](#) [E6](#) [E6](#) [FR](#) [HU](#) [IT](#) [JA](#) [KO](#) [NL](#) [NO](#) [PL](#) [PT](#) [RU](#) [SK](#) [TR](#) [ZH](#)

Detailed information for: ST201M-B10

This page contains technical data sheet, documents library and links to offering related to this product. If you require any other information, please contact us using form located at the bottom of the page.

[Print...](#)

[Print to Pdf...](#)

[Data Sheet](#)

[Downloads](#)

ST201M-B10

General Information

Extended Product Type:

ST201M-B10

Product ID:

2CDS271334R0105

EAN:

4016779017145

Catalog Description:

Miniature Circuit Breaker - ST200M - B

Long Description:

ST201M-B10 Miniature Circuit Breaker ST201M-B10 Miniature Circuit Breaker B-Char., 10kA, 10A, 1P

Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products »

Miniature Circuit Breakers MCBs



Technical

Standards:

CSA 22.2 No. 235

IEC/EN 60947-2

UL 1077

Tripping Characteristic:

B

Rated Ultimate Short-Circuit Breaking Capacity (I_{cu}):

(230 V AC) 15 kA

Rated Service Short-Circuit Breaking Capacity (I_{cs}):

(230 V AC) 11.2 kA

Terminal Type:

Double Clamp

Environmental

RoHS Status:

Following EU Directive 2011/65/EU

Technical UL/CSA

Interrupting Rating acc. to UL1077:

(277 V AC) 10 kA

(60 V DC) 10 kA

Dimensions

Product Net Width:

17.5 mm

Product Net Depth / Length:

69 mm

Product Net Height:

88 mm

Product Net Weight:

0.115 kg

Container Information

Package Level 1 Units:

carton 1 piece

Package Level 1 Width:

24 mm

Package Level 1 Depth / Length:

92 mm

Package Level 1 Height:

80 mm

Package Level 1 Gross Weight:

0.13 kg

Package Level 1 EAN:

4016779030700

Ordering

Minimum Order Quantity:

1 piece

Customs Tariff Number:

85362010

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:

[2CDK400679D2703](#)

Instructions and Manuals:

[9AKK107046A3150](#)

RoHS Information:

[2CDK400679D2703](#)

Popular Downloads

Data Sheet, Technical Information:

[9AKK107046A3150](#)

Instructions and Manuals:

[9AKK107046A3150](#)

Classifications

ETIM 6:

EC000042 - Miniature circuit breaker (MCB)

ETIM 7:

EC000042 - Miniature circuit breaker (MCB)

ETIM 8:

EC000042 - Miniature circuit breaker (MCB)

eClass:

V11.0 : 27141901

UNSPSC:

39121614

Contact us

Submit your inquiry and we will contact you

[CONTACT US](#)

Or contact your [ABB Contact Center](#)

