




# 1326028-1 Product Details

[Share](#) | [Print](#) | [Email](#)


1326028-1

## Miscellaneous Automotive

Converted to ELV Compliant (Statement of Compliance)

### Product Highlights:

- Contact
- Contact Configuration = Receptacle
- Mount = Wire Crimp
- Wire Range = 0.50-0.90<sup>2</sup> [20-18] mm [AWG]
- Gold Contact Plating, Mating Area, Material

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Internal Number: 1326028-1

Active

[View 3D PDF](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

## Documentation & Additional Information

### Product Drawings:

- [CONTACT, FEMALE, 0.64mm GOLD PLATED \(PDF, English\)](#)

### Catalog Pages/Data Sheets:

- None Available

### Product Specifications:

- [0.64 mm USCAR Contact System \(PDF, English\)](#)

### Application Specifications:

- [0.64 mm Contact System \(PDF, English\)](#)

### Instruction Sheets:

- [0.64 mm Automotive 32-Position Plug Connector Assembly \(PDF, English\)](#)
- [0.64 mm Automotive Sealed Plug Connectors \(PDF, English\)](#)
- [0.64mm Unsealed Dual-Row Automotive Plug Connectors ... \(PDF, English\)](#)

### CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version C\)](#)
- [3D Model \(IGES, Version C\)](#)
- [3D Model \(STEP, Version C\)](#)

### Additional Information:

- [Product Line Information](#)

### Related Products:

- [Tooling](#)

[List all Documents](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- [Product Type = Contact](#)
- [Finish = Gold \(30\)](#)

### Mechanical Attachment:

- [Mount = Wire Crimp](#)

### Termination Features:

- [Receptacle Size \(mm \[in\]\) = 0.64 \[0.025\]](#)

### Body Features:

- [Wire Range \(mm \[AWG\]\) = 0.50-0.90<sup>2</sup> \[20-18\]](#)

### Contact Features:

- [Contact Configuration = Receptacle](#)
- [Contact Plating, Mating Area, Material = Gold](#)
- [Contact Base Material = Copper Alloy](#)

### Industry Standards:

- [RoHS/ELV Compliance = ELV compliant](#)
- [Lead Free Solder Processes = Not reviewed for lead free solder process](#)
- [RoHS/ELV Compliance History = Converted to comply with ELV directive](#)

### Other:

- [Brand = AMP](#)

## Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

## Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

## Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

## Keep Me Informed

Receive TE News, Events & Technology Updates

