

**Product Details for 88189 - 8**



**88189 - 8**

[Active](#)

**Flexible Film Connectors**

[RoHS Compliant \(Statement of Compliance\)](#)

**Product Highlights:**

- ? [Housing](#)
- ? [2.54 mm Centerline](#)
- ? [Connector Type = Standard](#)
- ? [Number of Positions = 24](#)
- ? [Number of Rows = Dual](#)

[View all Features](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(4\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [HOUSING, PIN, DBL ROW, W/DETENT SLOTS, .100 CL, FFC](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? None Available

**Application Specifications:**

- ? [Flexible Flat Cable \(FFC\) Housings/w Contact Cavities](#) (PDF, English)

**Instruction Sheets:**

- ? None Available

**CAD Files:**

- ? None Available

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)
- ? [Mating Products \(4\)](#)

[List all Documents](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? [Product Type](#) = Housing
- ? [Connector Type](#) = Standard
- ? [Number of Positions](#) = 24
- ? [Mating Type](#) = Plug
- ? [Mating Connector Lock](#) = With
- ? Mating Connector Lock Type = Detent Windows
- ? [Mating Polarization](#) = With
- ? [Mounting Ears](#) = Without
- ? Shrouded = Yes
- ? Flame Retardant = Yes
- ? Color = Black

**Mechanical Attachment:**

- ? [Panel Attachment](#) = Without

**Body Related Features:**

- ? [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- ? [Number of Rows](#) = Dual

**Housing Related Features:**

- ? Housing Material = Thermoplastic
- ? Housing Flammability Rating = UL 94V -0

**Industry Standards:**

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

**Conditions for Usage:**

- ? [Terminate To](#) = FFC Cable

**Other:**

- ? Brand = AMP