


1445336-1 Product Details

Have a Question?

Chat with a Product Information Specialist



1445336-1

TE Internal Number: 1445336-1

Active

[View 3D PDF](#)

MTA, CST, CST-100 II and SL Contacts

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Contact Configuration = CST-100 II Contacts
- Crimp Termination Method to Wire/Cable
- Pre-Tin Contact Plating, Mating Area, Material
- Wire Size = 0.12-0.4² [26-22] mm² [AWG]
- Used For CST-100 II Housings

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [CONTACT, LOOSE PIECE, CST 100 II](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [CST-100 Type II .100 Inch Centerline Crimp-Snap Conn...](#) (PDF, English)

Application Specifications:

- [CST-100 II Connectors](#) (PDF, English)

Instruction Sheets:

- [Extracting CST-100 II Contact 1375819-\(\) from Housin...](#) (PDF, English)

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version A)
- [3D Model](#) (IGES, Version A)
- [3D Model](#) (STEP, Version A)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Termination Method to Wire/Cable](#) = Crimp
- [Wire Size \(mm² \[AWG\]\)](#) = 0.12-0.4² [26-22]
- Used For = CST-100 II Housings
- Wire Insulation Diameter (mm [in]) = 0.89 - 1.65 [0.035 - 0.065]
- Comment = Not for use in housing Part No. 770602.

Contact Related Features:

- Contact Configuration = CST-100 II Contacts
- Contact Plating, Mating Area, Material = Pre-Tin
- Contact Base Material = Phosphor Bronze

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- [Packaging Method](#) = Loose Piece

Other:

- Brand = AMP

BOOKMARK

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

