

182198-1 Product Details


Have a Question?

Chat with a Product Information Specialist



Quick Links


- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)



182198-1

TE Internal Number: 182198-1

 Active

 [View 3D PDF](#)

.156 Inch AMPMODU .031 X .062 Mod I

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Contact
- High Applied Pressure
- Packaging Method = Loose Piece
- Tin Contact Plating, Mating Area, Material
- Wire Range = 0.30-0.90² [22-18] mm [AWG]

[View all Features](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [l.p. cont. crimp on snap in amp modu i](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- [AMPMODU I Interconn. system](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing](#) (DXF, Version A)
- [3D Model](#) (IGES, Version A)
- [3D Model](#) (STEP, Version A)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Contact
- [Applied Pressure](#) = High
- Insulation Diameter (mm [in]) = 1.80-2.30 [.071-.091]

Termination Related Features:

- Termination End Plating = Tin (30)

Body Related Features:

- Wire Range (mm [AWG]) = 0.30-0.90² [22-18]

Contact Related Features:

- Contact Plating, Mating Area, Material = Tin
- Contact Base Material = Phosphor Bronze

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Applies To = Wire

Packaging Related Features:

- [Packaging Method](#) = Loose Piece

Other:

- Brand = AMP

 BOOKMARK 

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

