

1-1933400-0 Product Details

[Share](#) [Print](#) [Email](#)


1-1933400-0

TE Internal Number: 1-1933400-0

 [Active](#)

AMPINNERGY Manufactured Wiring Systems

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Product Category = AMPINNERGY Cable Assemblies
- AMPINNERGY Product Line
- Cable Assembly
- Cable Assembly Type = Power to Power Cable Assembly
- Cable Interface = Male (Power) / Male (Power)

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [CABLE ASSEMBLY, POWER TO POWER 3-3-2 \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Category = AMPINNERGY Cable Assemblies
- Product Line = AMPINNERGY
- Product Type = Cable Assembly
- Cable Assembly Type = Power to Power Cable Assembly
- Wiring System = 8-Wire/3 Circuits(3-3-2), Dedicated Neutral
- Neutral Wire Size (AWG) = 10 - 12
- UL File Number = E132626

Electrical Characteristics:

- Current Rating @ 125VAC (A) = 20

Body Features:

- Cable Interface = Male (Power) / Male (Power)
- Length (mm [in.]) = 3048.00 [120.000]
- Conduit Size (mm [in.]) = 14.29 [0.5625]
- Conduit Type = Flexible Metal Conduit

Housing Features:

- Housing Material = Polycarbonate
- Housing Color = Gray

Configuration Features:

- Cable Assembly Length (M [ft]) = 3.05 [10.000]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- Agency/Standard = UL
- UL Rating = Listed

Other:

- Brand = AMP
- Comment = Use with 3-3-2 wiring system only.

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

