


Product Details for 208294 - 2



208294 - 2

Non - Metallic Cable Splices and Tap

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? T-Tap Connector
- ? Number of Wires = 2 + ground

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Active](#)

Documentation & Additional Information

Product Drawings:

- ? [KIT, NONMETALLIC CABLE T -TAP, 2 CONDUCTOR + GROUND, ...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? [Nonmetallic Sheathed Cable Interconnection Devices](#) (PDF, English)

Instruction Sheets:

- ? [Nonmetallic \(Type NM -3\) Sheathed Cable T -Tap Con... \(1\)](#) (PDF, English)
- ? [Nonmetallic \(Type NM -3\) Sheathed Cable T -Tap Con... \(2\)](#) (PDF, English)

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = T -Tap Connector
- ? Product Series = NM -3
- ? Comment = Kit individually packaged in polybag containing 1 housing preloaded with contacts, 1 strain relief, 4 screws and 1 Instruction Sheet.; Box contains 10 kits.

Mechanical Attachment:

- ? Strain Relief Material = Polycarbonate

Electrical Characteristics:

- ? Current Rating (Amps.) = 20

Body Related Features:

- ? Number of Wires = 2 + ground
- ? Wire Range (mm [AWG]) = 2.00 -3.00 ² [14-12]
- ? Wire Type = Solid
- ? Strain Relief Color = Clear

Contact Related Features:

- ? Contact Material = Copper Alloy
- ? Contact Mating Area Plating = Tin

Housing Related Features:

- ? Housing Material = Polycarbonate
- ? Housing Color = Soft White

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? Packaging Method = Kit
- ? Packaging Quantity = 1, 10 Kits/Box

Other:

- ? Brand = AMP