


5205732 -1 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



5205732 -1

[Active](#)

Cable Clamps

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Backshell/Cable Clamp
- ? Cable Clamp Type = Clam Shell
- ? Straight(180°)/45° Cable Exit Angle
- ? Cable Insulation Diameter = 15.24 mm
- ? Shell Size = 5

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [SELF TAPPED 45/180 DEG CABLE SUPPORT CLAMSHELL, SIZE...](#)
(PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? [Cablej Clamp Assemblies for AMPLIMITE HD -20 and HD -2...](#)
(PDF, English)

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Backshell/Cable Clamp
- ? [Cable Clamp Type](#) = Clam Shell
- ? [Shell Size](#) = 5
- ? [Shielded](#) = No
- ? [Screws and Retainer Clips](#) = Without
- ? [Grommets](#) = Without
- ? Thread Size = 6 -32
- ? Product Series = HDP Metal Shell
- ? Clam Shell Length = Standard
- ? Comment = All parts are packaged unassembled.

Body Related Features:

- ? [Cable Exit Angle](#) = Straight(180°)/45°
- ? [Cable Insulation Diameter \(mm \[in\]\)](#) = 15.24 [0.600]
- ? Cable Clamp Material = Thermoplastic
- ? Shield Plating = None

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? [Packaging Method](#) = Individual Kit

Other:

- ? Brand = AMP