

**Product Details for 5447650 - 3**

**SMA/QMA RF Connectors**

[RoHS Compliant \(Statement of Compliance\)](#)


**Product Highlights:**

- ? Connector
- ? Jack
- ? Connector Type = SMA
- ? Terminate To Coaxial Cable
- ? Coaxial Cable Termination Type = Crimp

[View all Features](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)



**5447650 - 3**

[Active](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [CONNECTOR, JACK, BULKHEAD, SMA, HEX CRIMP, COMMERCIAL](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? None Available

**Application Specifications:**

- ? None Available

**Instruction Sheets:**

- ? None Available

**CAD Files:**

- ? None Available

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)

[List all Documents](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? [Product Type](#) = Connector
- ? [Gender](#) = Jack
- ? [Connector Type](#) = SMA
- ? [Crimp Type](#) = Hex
- ? [Body Style](#) = Straight
- ? [Body Material](#) = Brass
- ? [Body Finish](#) = Nickel
- ? [Center Contact](#) = With

**Mechanical Attachment:**

- ? [Panel Attachment](#) = With
- ? [Panel Attachment Method](#) = Bulkhead
- ? [Panel Attachment Style](#) = Rear Mount

**Electrical Characteristics:**

- ? Frequency = 12.4 GHz (Max.)

**Termination Related Features:**

- ? [Coaxial Cable Termination Type](#) = Crimp

**Body Related Features:**

- ? [Length \(mm \[in\]\)](#) = 27.43 [1.080]
- ? Center Contact Crimp Setting = 4

**Configuration Related Features:**

- ? [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 174, 188A, 316

**Industry Standards:**

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

**Conditions for Usage:**

- ? [Terminate To](#) = Coaxial Cable

**Other:**

- ? Brand = AMP