

2-1991253-5 Product Details

 [Share](#) |
  [Print](#) |
  [Email](#)



2-1991253-5

Cable Clamps

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:


- Backshell/Cable Clamp
- Cable Clamp Type = Clam Shell
- 180° Cable Exit Angle
- Cable Insulation Diameter = 3.00 - 11.00 mm
- 25 Positions





[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Internal Number: 2-1991253-5

 [Active](#)

 [Add to My Part List](#) |
  [Request Sample](#) |
  [Find Similar Products](#) |
  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [LOW COST PLASTIC D-SUB BACKSHELL](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Backshell/Cable Clamp
- [Cable Clamp Type](#) = Clam Shell
- [Shell Size](#) = 3
- [Screws and Retainer Clips](#) = With
- [Grommets](#) = Without
- [Slide Latch](#) = Without
- Thread Size = 4-40
- Clam Shell Length = Standard

Electrical Characteristics:

- [Shielded](#) = No

Body Features:

- [Cable Exit Angle](#) = 180°
- [Cable Insulation Diameter \(mm \[in\]\)](#) = 3.00 - 11.00 [0.118 - 0.433]
- Number of Positions = 25
- Cable Clamp Material = Thermoplastic
- Shield Plating = None

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Packaging Features:

- [Packaging Method](#) = Bulk
- Packaging Quantity = 100 Pieces

Other:

- Brand = Tyco Electronics

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address 

