




## SSB6TE050101 Product Details

[Share](#) | [Print](#) | [Email](#)


SSB6TE050101

TE Internal Number: 6-1437414-4



Search for Replacement Parts

### Barrier Strips

Not reviewed for RoHS Compliance

#### Product Highlights:

- Barrier Strip
- Barrier Style = Single Row, Dual Barrier
- Block Style = Turret
- 9.53 mm Centerline
- Vertical Mount Angle

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Barrier Strip
- [Block Style](#) = Turret
- [Mount Angle](#) = Vertical
- [Screw Material](#) = Steel
- [Mounting Insert](#) = With

#### Mechanical Attachment:

- [Mounting Options](#) = Open End Positions With Inserts
- [Screw Plating](#) = Bright Zinc/Chrome
- [Mounting Style](#) = Open End Position
- [Mounting Ears](#) = With

#### Electrical Characteristics:

- [Top Hardware](#) = Binding Combo Head

#### Body Features:

- [Barrier Style](#) = Single Row, Dual Barrier
- [Terminal Style](#) = Solder Tail 12.19 [.480]

#### Housing Features:

- [Centerline \(in \[mm\]\)](#) = 0.375 [9.53]

#### Configuration Features:

- [Number of Positions](#) = 5
- [Number of Levels](#) = Single

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process

#### Other:

- [Brand](#) = Buchanan
- [Comment](#) = Other options available upon request, consult our Product Information Center.

### Corporate Information

[About TE](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)  
[Terms & Conditions](#)  
[Privacy Policy](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference Products](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

