

## 1-1478762-5 Product Details

Have a Question?

Chat with a Product Information Specialist



1-1478762-5

TE Internal Number: 1-1478762-5

Active

View 3D PDF

### Cable Clamps

Always EU RoHS/ELV Compliant ([Statement of Compliance](#))

#### Product Highlights:

- Backshell/Cable Clamp
- Cable Clamp Type = Straight
- 180° Cable Exit Angle
- Cable Insulation Diameter = 4.00 - 13.00 mm
- 15 Positions

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [AM STRAIGHT ENTRY](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version F)
- [3D Model](#) (IGES, Version F)
- [3D Model](#) (STEP, Version F)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Backshell/Cable Clamp
- Cable Clamp Type = Straight
- [Shell Size](#) = 2
- [Screws and Retainer Clips](#) = With
- [Grommets](#) = With
- [Slide Latch](#) = Without
- Thread Size = 4-40
- Product Series = ADK
- Number of Grommets Per Set = 4
- Comment = Kit includes backshells, jackscrews and cable grommets.

#### Electrical Characteristics:

- [Shielded](#) = Yes

#### Body Related Features:

- [Cable Exit Angle](#) = 180°
- [Cable Insulation Diameter \(mm \[in\]\)](#) = 4.00 - 13.00 [0.158 - 0.512]
- Number of Positions = 15
- Cable Clamp Material = Die Cast
- Shield Plating = Nickel

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- [Packaging Method](#) = Bulk
- Packaging Quantity = 100 Pieces

#### Other:

- Brand = AMP

BOOKMARK

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

### Follow Us On:



### Visit Us On:

