




4-5353184-0 Product Details

[Share](#) | [Print](#) | [Email](#)


0.6mm Free Height

.6FHP04H,140,S,GIG,30/Sn,TR,NSYes

4-5353184-0

TE Internal Number: 4-5353184-0

Active

[View 3D PDF](#)

Product Highlights [View All](#)

- Connector
- Connector Style = Plug
- Family Name = Free Height
- .60 mm Centerline
- 140 Positions

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Type	Connector
Family Name	Free Height
PCB Mounting Orientation	Vertical
Keyed	Yes
Sealant	Without
Dimensions	
Board-to-Board Stack Height (mm [in])	4.00 [0.157]
Body Features	
Grounding Plate	With
Locating Post(s)	With
Vacuum Cover	Without
Contact Features	
Contact Layout	In-Line
Contact Base Material	Copper Alloy
Contact Plating, Mating Area, Material	Gold (30)
Grounding Contact	With
Solder Tail Contact Plating	Tin
Housing Features	
Connector Style	Plug
Centerline (mm [in])	0.60 [0.024]
Housing Material	Thermoplastic
Housing Material Temperature	High

Configuration Features	
Number of Positions	140
Preloaded	Yes
Number of Rows	Dual
Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Reflow solder capable to 245°C, Reflow solder capable to 260°C
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0
Conditions for Usage	
Applies To	Printed Circuit Board
Operation/Application	
Industry Application	Board-to-Board (Personal Systems/Computers), Networking (Communications)
Packaging Features	
Packaging Method	Tape & Reel
Product Availability	
Region	Americas
Other	
Brand	TE Connectivity

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

