


1487595-1 Product Details



1487595-1

TE Internal Number: 1487595-1

[Active](#)

Cable Assemblies

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Industry Standard Cable Assembly Category
- Cable Assembly Type = Universal Serial Bus (Standard)
- Input/Output (I/O) Application
- Assembly Type = USB 4 Position Plug, Type A to Type B
- Double Ended Configuration

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Have a Question?

Chat with a Product Information Specialist

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [CABLE ASSEMBLY, USB A TYPE TO USB B TYPE](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Cable Assembly Category = Industry Standard
- Cable Assembly Type = Universal Serial Bus (Standard)
- [Assembly Type](#) = USB 4 Position Plug, Type A to Type B
- [Color](#) = Black
- [Wire Size \(mm² \[AWG\]\)](#) = 2/28,2/26
- Keyed = No

Mechanical Attachment:

- Configuration = Double Ended

Electrical Characteristics:

- Shielded = Yes

Body Related Features:

- [Number of Positions](#) = 4
- [Length \(M \[ft\]\)](#) = 1.00 [3.281]
- [Equalized](#) = No

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- [Application](#) = Input/Output (I/O)

Other:

- Brand = AMP

BOOKMARK

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

