



204512-2 Product Details

Share Print Email



204512-2

TE Internal Number: 204512-2

Active

Subminiature D Pins/Sockets for MIL-C-24308 and MIL-C-39029

Not EU RoHS or ELV Compliant (Find RoHS Compliant Alternates)

Product Highlights:

- Connector
- Product Series = 90
- Connector Style = Receptacle
- Contact Type = Socket
- Density = High

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- [AMPLIMITE KIT, HDD SERIES RECEPTACLE, SIZE 1, 15 POS... \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- [AMPLIMITE High Density 22 \(HD-22\) Connectors \(PDF, English\)](#)

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Insert Arrangement](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Product Series](#) = 90
- [Shell Size](#) = 1
- [Shell Material](#) = Steel
- [Termination Method to Wire/Cable](#) = Crimp
- [Mounting Hole Diameter \(mm \[in\]\)](#) = 3.05 [.120]

Body Features:

- [Blindmate](#) = No
- [Non-Magnetic](#) = No
- [Rear Grommet](#) = No
- [Power/Signal/Coax Combination](#) = No
- [Shell Plating](#) = Cadmium
- [Mount Style](#) = Mounting Holes
- [Retention Clip Material](#) = Stainless Steel

Contact Features:

- [Contact Type](#) = Socket
- [Contact Size](#) = 22
- [Contact Style](#) = Crimp Snap-in

Housing Features:

- [Connector Style](#) = Receptacle

Configuration Features:

- [Density](#) = High
- [Number of Positions](#) = 15

Industry Standards:

- [Government/Industry Qualification](#) = Yes
- [Government/Industry Part Number](#) = M24308/2-11F
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [NASA Qualification](#) = No

Conditions for Usage:

- [Applies To](#) = Wire/Cable

Other:

- [Brand](#) = AMP
- [Comment](#) = Size 22 sockets supplied with receptacles are loose piece.; "F" is stamped on connectors following M24308 part number as required. "F" designates cadmium shell plating.

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

