



1-1337418-0 Product Details

[Share](#) | [Print](#) | [Email](#)


N Series RF Connectors

N Pnl Skt 50Ohm Silver Pltd

1-1337418-0

TE Internal Number: 1-1337418-0

Active

[View 3D PDF](#)

Product Highlights [View All](#)

- Connector - RF
- Jack
- Coaxial Cable Termination Type = Solder
- Applies To Wire/Cable
- Body Style = Straight

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

Documents

Features

Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Type	Connector - RF
Gender	Jack
Grade	Commercial
Lightning/EMP Protection	None
Dielectric Material	PTFE
Weatherproof	No
Mechanical Attachment	
Panel Mount Retention	With
Panel Mount Retention Type	Flanged
Panel Attachment Style	Front Mount, Rear Mount
Panel Cutout	1 x 16.1 + 4 x 3.2
Flange Dimension [Sq.] (mm [in])	25.40 [1.000]
Electrical Characteristics	
Frequency	DC - 11 GHz
Connector Impedance (Ω)	50
Termination Features	
Coaxial Cable Termination Type	Solder
Body Features	
Body Style	Straight
Body Plating	Silver
Body Material	Brass
Flange and Thread Material	Brass

Contact Features	
Captured Center Contact	With
Center Contact Plating	Silver
Center Contact Material	Brass
Configuration Features	
Solder Terminal	With
Industry Standards	
Government/Industry Qualification	No
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
RoHS/ELV Compliance History	Always was RoHS compliant
Military Style Number	UG-58A/U
Environmental	
Operating Temperature (Max.) (°C)	165
Conditions for Usage	
Applies To	Wire/Cable
Packaging Features	
Packaging Method	Individual
Packaging Quantity	50
Other	
Brand	Greenpar

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

