


880124 Product Details

[Share](#) [Print](#) [Email](#)



880124

TE Internal Number: 880124

 **Active**

 [View 3D PDF](#)

.240, .295" Centerline, 250 v, 28 A max. (.140" MATE-N-LOK)

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- Housing
- 6.10 x 6.10 mm Centerline, Matrix
- Connector Style = Plug
- Contact Type = Socket

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(3\)](#)
- [View Contacts \(29\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [9 circuit 140 dia plug](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [.140 Diameter MATE-N-LOK Pin and Socket Connector](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing](#) (DXF, Version C)
- [3D Model](#) (IGES, Version C)
- [3D Model](#) (STEP, Version C)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)
- [Mating Products \(3\)](#)
- [Contacts \(29\)](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- Connector Type = Housing
- [Mount](#) = Free Hanging
- [Color](#) = Natural
- Connector Line = .140 MATE-N-LOK
- Lock Type = Positive Lock

Electrical Characteristics:

- Voltage (VAC) = 250

Body Features:

- Centerline, Matrix (mm [in]) = 6.10 x 6.10 [.240 x .240]
- Number of Positions = 9

Contact Features:

- Contact Type = Socket
- Contact Layout = Matrix

Housing Features:

- Connector Style = Plug
- Housing Material = Nylon

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = AMP

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)


Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

